



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

2N5172

Silicon NPN Transistor Audio Power Amplifier TO-92 Type Package

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$, Note 1 unless otherwise specified)

Collector-Base Voltage, V_{CBO}	25V
Collector-Emitter Voltage, V_{CEO}	25V
Emitter-Base Voltage, V_{EBO}	5V
Collector Current, I_C	500mA
Total Device Dissipation, P_D	625mW
Derate Above $+25^\circ\text{C}$	5.0mW/ $^\circ\text{C}$
Operating Junction Temperature Range, T_J	-55° to $+150^\circ\text{C}$
Storage Temperature Range, T_{stg}	-55° to $+150^\circ\text{C}$
Thermal Resistance, Junction-to-Case, R_{thJC}	83.3 $^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient, R_{thJA}	200 $^\circ\text{C/W}$

Note 1. These ratings are limiting values above which the serviceability of any device may be impaired.

Note 2. These are steady state limits and are based on a maximum junction temperature of 150°C .

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 10\mu\text{A}$, $I_E = 0$	25	–	–	V
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 10\text{mA}$, $I_B = 0$, Note 3	25	–	–	V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 10\mu\text{A}$, $I_C = 0$	5	–	–	V
Collector Cutoff Current	I_{CBO}	$V_{CB} = 25\text{V}$, $I_E = 0$	–	–	100	nA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = 5\text{V}$, $I_C = 0$	–	–	100	nA
DC Current Gain	h_{FE}	$V_{CE} = 10\text{V}$, $I_C = 10\text{mA}$, Note 3	100	–	500	–
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10\text{mA}$, $I_B = 1.0\text{mA}$, Note 3	–	–	0.25	V
Base-Emitter On Voltage	$V_{BE(on)}$	$V_{CE} = 10\text{V}$, $I_C = 10\text{mA}$, Note 3	0.5	–	1.2	V
Small-Signal Current Gain	h_{fe}	$I_C = 10\text{mA}$, $V_{CE} = 10\text{V}$, $f = 1.0\text{ kHz}$	100	–	750	pF
Collector-Base Capacitance	C_{cb}	$V_{CB} = 10\text{V}$, $f = 1.0\text{ MHz}$	1.6	–	10	pF

Note 3. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 2\%$.

