© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD TERMINALS







✔ Active

TE CONNECTIVITY (TE)

MIC MK-2 TAB CONTACT

85034-1
TE Internal Number: 85034-1

EU RoHS Compliant
EU ELV Compliant

Terminal & Splice Style Tab

Terminal Transmits 0 – 24 A (Low Power)

Wire Size (mm²) .5 – 2

Sealable No

Wire Size Search (AWG) 14, 15, 16, 17, 18, 19

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION —

Product Drawings

MIC MK-II TAB CONTACT
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealable No

Contact Features

Crimp Type F-Crimp
Terminal & Splice Style Tab
Interface Plating Tin (Sn)
Contact Termination Area Plating Material Tin (Sn)

Termination Features

Termination Method Crimp

Dimensions

Wire Size (mm²) .5 – 2
Wire Size Search (AWG) 14, 15, 16, 17, 18, 19
Wire Size Search (mm²) .5, .6, .75, .85, 1, 1.25, 1.3, 1.5, 2
Wire Insulation Diameter 2.16 – 3.43 mm [.085 – .135 in]

Packaging Features

Packaging Quantity 5000
Packaging Method Reel

Other

Terminal Transmits 0 – 24 A (Low Power)

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.

Downloaded from Arrow.com.