

8

7

6

5

4

3

2

I

© 2020 TE Connectivity. All Rights Reserved.

LOCKING UNIT POSITION UPPER
CABLE OUTLET POSITION 3

1:2

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

DIE ZEICHNUNG ZEIGT DEN 2-DIMENSIONALEN IDEALZUSTAND DES ZUSAMMENBAUTEILS BEZÜGLICH DER KOMPONENTEN ZUR IDENTIFIKATION UND SPEZIFIKATION DER NOTWENDIGEN DIMENSIONEN. HINSICHTLICH DER ORIENTIERUNG UND DER LAGE DER KOMPONENTEN (Z.B. BIEGESCHLAPPE KABEL) KÖNNEN DIE DELIEFERTEN TEILE VON DER ZEICHNUNG ABWEICHEN, SOFERN DIE FUNKTIONALITÄT NICHT BEEINTRÄCHTIGT IST.

INTERFACE VIEW
Schnittstellen Ansicht

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E	1	PACKAGING CHANGED	23JUN2016	OS	JJ
F		COMPONENT (CABLE, 2 x 0.75 mm²) REVISED	19NOV2018	JM	JJ
G		ITEM NO. 5 (INSULATION COVER) REVISED	01OCT2020	JM	JJ

1

2

3

4

5

6

7

8

9

10

11

12

13

18

17

16

14

15

2

100 ±15

L

(50)

LENGTH SCHEDULE:
Laengentabelle:

TE PART NO.	REV.	LENGTH L (mm)	TOL.	CABLE OUTLET POSITION
2-2208884-1	G	1000	+30	Position 3
2-2208884-5	G	5000	+60	

NOTES

1

PACKAGING ACCORDING SPECIFICATION V2208884.

2

STRIPPED ONLY OUTER JACKET AND BRAID. ELECTRICAL TESTING IS ACCORDING APPLICATION SPECIFICATION.

APPLICATION SPECIFICATION:
114-94163-2 CHARGE INLET IEC 62196-2 TYPE 11.

CUTTING LENGTHS TO BE FIXED BY MANUFACTURING.

5

MANUFACTURING CODE:
TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY).
TO BE PRINTED ON LABEL (ITEM 17).
LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.

WIRING SCHEDULE:
Belegungsplan:

CAVITY-NO.	IDENTIFICATION	WIRE COLOUR	WIRE SECTION
1	L1	RED	6mm² (ITEM 14)
2	N	BROWN	6mm² (ITEM 14)
3	GROUND/EARTH	BROWN	6mm² (ITEM 15)
4	CP	BROWN/WHITE	0.75mm² (ITEM 16)
5	PP	WHITE	0.75mm² (ITEM 16)

5

LABEL LEGEND:
Label Beschriftung:

TE PN: X-2208884-Y Rev. --

DD/MM/YY

2 kV TESTED

TE PART NO., CURRENT REVISION
TE Teilenummer, aktuelle Revision

PRODUCTION DATE
Produktionsdatum

3	CAB TIE, CLIP, HELL, T18R-HR-N46	18
1	LABEL, HELL	17
see table	CABLE, 2 x 0.75 mm², BLACK	16
see table	CABLE, 6 mm², BROWN	15
see table	CABLE 2 x 6.0 mm², BRAID	14
2	O-RING, 3 x 1.5	13
3	O-RING, 4 x 1.5	12
1	PIN DIA 3.0, PP	11
1	PIN DIA 3.0, CP	10
1	PIN DIA 6.0, PE	9
2	PIN DIA 6.0, L/N, ASSY	8
3	SELF TAPPING SCREW	7
2	FAMILY SEAL, MIXED, Vers.1	6
1	INSULATION COVER, TE, COVER INLET	5
1	CABLE FIXATION, TE, COVER INLET	4
1	ACTUATOR, LOCKING UNIT, ASSY	3
1	2. LOCK, TE, IEC62196-2 TYPE 2	2
1	5 POS. MIXED, HSG, IEC 62196-2 TYPE 2	1
QTY X- -Y	DESCRIPTION	ITEM NO.
-	WEIGHT OF ASSY NO. [g]	

PRODUCT CHARACTERISTICS ACC. QMP EMEA_12
BESONDERE MERKMALE NACH QMP EMEA_12

TOLERANCING ISO 8015
TOLERIERUNG ISO 8015

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)

DWN M. Zelch 06JUN2013
CHK J. Bernstorf 06JUN2013
APVD M. Folk 10JUN2013

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

WEIGHT

CUSTOMER DRAWING

2- -X AS SHOWN
wie dargestellt

TE Connectivity

NAME HV, CHARGE INLET TYPE 2,
HYB ASSY, 6 sqmm
LOCKING UNIT POSITION UPPER

SIZE CAGE CODE DRAWING NO
A 00779 ©=2208884

RESTRICTED TO

SCALE 1:1 SHEET 1 OF 1 REV G

4805 (3/13)

Downloaded from Arrow.com