


© 1963 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. APPROVED PER GOVT CONTRACT NO.

CAVITY IDENTIFICATION ON P/N'S
(1) 582557-1 AND (1) 582557-2 ONLY.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	R	REVISED PER 0600-3683-95 TA	10-75	J. WARNER
	S	ECO-08-020973	PY 11-08	JW




582557-1 1. AS SHOWN. "J" DIA. HOLES = .156
OBS. 582557-2 1. SAME AS -1 EXCEPT:
2. "J" DIA. HOLES = .128

OBS. 582557-4 1. SAME AS -1 EXCEPT:
2. FLOATING BUSHINGS.


OBS. 582557-5 1. SAME AS -4 EXCEPT:
BUSHINGS REVERSED.
(1) 582557-1 1. SAME AS -1 EXCEPT TO HAVE CAVITY IDENT. ON TOP SURFACE OF HOUSING.
(1) 582557-2 1. SAME AS -2 EXCEPT TO HAVE CAVITY IDENT. ON TOP SURFACE OF HOUSING.

CLEARANCE FOR
#4 SCREW



-4
-5 BUSHING REVERSED
AS SHOWN

FIT FOR 1/16 P.C. BOARD
(.055-.070)



AMP-TAB CONTACTS
#66143 (WIRE #26-#22)
#66144 (WIRE #20)
MUST BE ORDERED
SEPARATELY

SECTION A-A

NOTE:

- UPPER CASE LETTERS. OMIT LETTERS G, I, O, & Q. CIRCUIT CAVITY IDENTIFICATION MARKING PER MIL-C-21097.
- GROOVES FOR "ON CONTACT KEYING" AMP'S OPTION DEPENDING ON METHOD OF MANUFACTURE. FOR "ON CONTACT" KEYING USE KEYING PLUG D/N 583487-1 (MUST BE ORDERED SEPARATELY.)
- LASER MARKING ACCEPTABLE FOR ALL MARKING

AMP INFO
LOC PRINT BY
1 F 10

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON			CONTRACT NO.		AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
FRACTIONS ±	DECIMALS ± .005	ANGLES ±	DR J. Asch	DATE 6-7-67	NAME 22 POSITION AMP-TAB CONNECTOR .100 CENTERS DUAL	
MATERIAL SEE CALLOUT			CHK S. Hilde	DATE 3/1/67	SIZE C	
HEAT TREAT SEE CALLOUT			APPD P. Hilde	DATE 12/1/67	CODE IDENT NO 00779	
FINISH SEE CALLOUT			DSGN APPD C. Hilde	DATE 12/1/67	NUMBER 582557	
			OTHER APPD		REV S	
					SCALE 4-1	
					WT. CALC. ACTUAL. SHEET	