








P.C.B. SOLDER LAND DIMENSION



Direction

Connection

A

1 = 4

B

1 = 2

C

1 = 6

D

1 = 5

E (push)

1 = 3

Specification:

Contact rating: 15V DC, 20mA

Contact resistance: 100mOhm max

Insulation resistance: 100MOhm min

Dielectric strength: 100V AC for the duration of 1 minute

Operating temperature: -40°C to +85°C

Operating force: center push: 500gf ±150gf

4-directional: 280gf ±100gf

Operating travel: lever: 8° ±2°

push: 1.0 ±0.2 mm

Soldering conditions: manual soldering:

- soldering temperature: 400°C max.

- soldering time: 4sec.

reflow soldering conditions:


- preheat: 150-175°C, 40-80sec.

- peak: 260°C, 1-4sec.; 2times max.




Tolerances: ±0.3mm			Date	Name	TSSJ 30	
			06/04	us		
P.C.B. Layout	03/14	dr			30 04 61	
Soldering conditions	06/13	dr				
Stem shape	06/10	dr				
Operating temperature	08/07	dr				
Packaging	11/05	dr				
Modifications	Date	Name			knitter-switch	
					Page	
					1/2	


Packaging:




INNER BOX



VINYLE WRAPPER



OUTER BOX



INSIDE OF INNER BOX



Tolerances: $\pm 0.3\text{mm}$			Date	Name	TSSJ 30	
			06/04	us		
						30 04 61
Modifications		Date	Name			Page
						2/2