4-1775099-2 ✔ ACTIVE

ATX Power


TE Internal #: 4-1775099-2


PCB Mount Header, Vertical, Wire-to-Board, 8 Position, 1.4 mm [.055 in] Centerline, Tin (Sn), Through Hole - Solder, Power, Ivory, Tray, ATX Power

View on TE.com >

Connectors > PCB Connectors > PCB Headers & Receptacles







PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **8**

Centerline (Pitch): **1.4 mm [.055 in]**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC

Body Features

Primary Product Color	Ivory

Downloaded from Arrow.com.

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Mating Tab Width	1.14 mm[.044 in]
PCB Contact Termination Area Plating Material Thickness	3.05 µm[120.07 µin]
Contact Layout	Matrix
Mating Tab Thickness	1.1 mm[.043 in]
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	3.05 µm[120.07 µin]
Contact Type	Pin
Contact Current Rating (Max)	9 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Rectangular Termination Post & Tail Width	1.14 mm[.044 in]
Rectangular Termination Post & Tail Thickness	.55 mm[.021 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarization
PCB Mount Alignment	Without
Mating Retention	Without
PCB Mount Retention	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Centerline (Pitch)	1.4 mm[.055 in]
Housing Material	PA 9T

Dimensions

Row-to-Row Spacing	4.2 mm[.165 in]

Usage Conditions

Operating Temperature Range	-25 – 85 °C[-13 – 185 °F]

Downloaded from Arrow.com.

Operation/Application

Circuit Application	Power

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts

Downloaded from Arrow.com.



TE Part # 3-1775099-2
ATX PWR CONN 1 BDLK 8 POS


Also in the Series | ATX Power



PCB Headers & Receptacles(35)



Rectangular Power Connectors(35)



Wire-to-Board Headers & Receptacles (32)

Customers Also Bought



TE Part #CAT-P97-F2090
Very High Performance, FN2090, Multi stage AC/DC EMC/RFI Filter with Excellent Attenuation Performance



TE Part #CSI-SGFB-100-UFFR
SMA to U.FL/MHF1 100mm 1.13 OD




TE Part #342144-1
16-14 F.E.P/G RING TONGUE




TE Part #917686-1
2.5 SIGNAL D/LOCK PLUG HSG 2P



TE Part #4-1473562-3
RITS CONN. PLUG ASSY 3P GREEN



TE Part #2-1775099-0
ATX PWR CONN 2 BDLK 4 POS



TE Part #6-2176307-3
RP 1E 0.1W 54K9 0.1% 25PPM 5K RL



TE Part #5-2176337-7
CRGCQ 0402 470K 1%



TE Part #5223957-1
UPM GUIDE MODULE

Downloaded from Arrow.com.

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1775099-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1775099-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1775099-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Product Specification

Japanese

AMP Mini CT Connector 1.5mm Pitch (Crimp Type), Lead Free Version

Japanese

Downloaded from Arrow.com.