Part Number : 351800404
Product Description : VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue
Series Number : 35180
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

351800404_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

351500000AS_ENG-000.pdf

351500000AS_KOR-000.pdf

PK-35180-001-001.pdf

351800400-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35180
Description	VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	756054258293

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	4
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	5.920/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	8.00mm, 8.70mm
Pitch - Termination Interface	8.00mm, 8.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type A, Natural	351810200
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Natural	351810210
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Blue	351810214
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural	359650200
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Blue	359650204
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural	359650210
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Blue	359650214
VersaBlade Multi-Module Hybrid	359659200

Downloaded from Arrow.com.

Plug Housing, 2 Circuits, Positive Lock, Type A, Natural, Glow-Wire Capable	
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Yellow, Glow-Wire Capable	359659203
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural, Glow-Wire Capable	359659210
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Yellow, Glow-Wire Capable	359659213

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.70mm Pitch, 2 Circuits, Natural	351820290
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.70mm Pitch, 2 Circuits, Red	351820292
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	2270298400
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	2270288400
VersaBlade Male Crimp Terminals	35745
VersaBlade Female Crimp Terminals	35746
VersaBlade Male Crimp Terminals	35747
VersaBlade Female Crimp Terminals	35748

Downloaded from Arrow.com.