

16 NEB/J 25


Power supply connectors



Power supply chassis socket,
for plugs 5.5 mm x 2.5 mm, straight version, with fixing
flange, break contact and solder eyes

16

NEB/J 25



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body POM, HB according to UL94
Contact Cu alloy, nickel-plated/silver-plated
Insulation PBT GF (may be PF in a transitional phase)

Mechanical data

Diameter opening 6.3 mm
Diameter center pin 2.35 mm
Mating cycles 5000¹
Insertion force 4–20 N¹
Withdrawal force 3–15 N¹

¹ measured with a gauge plug

Electrical data (at T_{amb} 20 °C)

Contact resistance ≤ 30 mΩ
Rated current 1 A
Rated voltage 12 V DC
Rated impulse voltage 500 V/60 s
Insulation resistance ≥ 100 MΩ

Associated products

Counterparts
 1614 20  1633 04  1634 02
 NES/J 25  NES/J 250  XNES/J 250

16

NEB/J 25

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
NEB/J 25	2	250	750

Packaging:

in bulk, in a cardboard box or a plastic bag