




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.


CUSTOMER DRAWING

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	N/A	FIRST RELEASE	09/25'17	IP
2	N/A	UPDATE P/N	10/31'17	IP
3	N/A	UPDATE KEEP OUT AREA FOR PLUG MATING	11/23'17	IP
4	N/A	REMOVE "-" OF P/N	01/10'18	IP
5	N/A	CHANGE THE D/C RULE FROM YYWWD TO YYWW	2/28'18	IP
6	N/A	CHANGE THE D/C Position character FROM YYWWD TO YYWW	4/10'18	IP
7	N/A	ADDING PACKING SPEC	6/7'18	IP
8	N/A	ZOOMING PCB VIEW	6/8'18	IP
9	N/A	CHANGING THE PACKING CARRIER	8/13'18	IP
10	N/A	CHANGING THE PACKING CARRIER WIDTH	8/21'18	IP
11	N/A	ADDING TWO CIRCULAR HOLES ON THE COVER SURFACE TO DISTINGUISH THE DIRECTION AND ADDING HOUSING COLOR DESCRIPTION	11/9'18	IP
12	N/A	CHANGING THE POST DIAMETER TOLERANCE	11/02'23	Tony






Remark:
PRINTED D/C AREA
印刷日期代码区域
YYWW
WEEK(周)
YEAR(年)




UNLESS OTHERWISE SPECIFIED TOLERANCES			APPROVAL		DATE	Amphenol Amphenol East Asia Limited				
U.S. METRIC			DRAWN	Danen.Wang	11/02'23					
.X	+/-	0.50	CHECKED	Tony.Tang	11/02'23	TITLE CUSTOMER DRAWING FOR SLIMLINE SAS X8 VERTICAL				
.XX	+/-	0.25	CHECKED							
.XXX	+/-	0.20	DRAWING FILE :							
FRACTIONS	+/-		DRAWING\U10\U10BH74X2X01X-12							
ANGLES	+/-	3°	ANGLE OF PROJECTION							
FOR MATERIALS AND FINISHES SEE NOTES			REMOVE SHARP EDGES							
DIMENSIONS			U.S. INCHES							
(METRIC)			(MM)							
						SIZE A3		DRAWING NO. U10BH74X2X01X		REV. 12
			SCALE			NONE		SHEET 1 OF 2		

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		



- NOTES:
- MATERIAL:
HOUSING : SOLDER REFLOW PROCESS COMPATIBLE LCP,BLACK, UL94V-0
CONTACTS : HIGH PERFORMANCE COPPER ALLOY,PLATING REFER TO P/N SYSTEM
LATCH : STAINLESS STEEL, SOLDERABLE NICKEL OVER ALL
 - RoHS COMPLIANT
 - ORDER P/N SYSTEM:
U10BH74XXX01X
- Packing Options
T: tape&reel
- Options (resonance damping and latch options)
1: With resonance damping
0: No resonance damping
- LATCH PIN LENGTH OPTIONS
2:1.5
4:2.2
5:3.0
6:4.2
- CONTACT PLATING OPTION
2:30 MICROINCHES OF GOLD ON MATING END WITH MATTE TIN ON SOLDER TERMINATION, NICKEL UNDERPLATE ALL OVER
3:15 MICROINCHES OF GOLD ON MATING END WITH MATTE TIN ON SOLDER TERMINATION, NICKEL UNDERPLATE ALL OVER



UNLESS OTHERWISE SPECIFIED TOLERANCES			APPROVAL		DATE		Amphenol Amphenol East Asia Limited					
U.S. METRIC			DRAWN		Danen.Wang 11/02'23							
.X +/- 0.50			CHECKED		Tony.Tang 11/02'23		TITLE CUSTOMER DRAWING FOR SLIMLINE SAS X8 VERTICAL					
.XX +/- 0.25			CHECKED									
.XXX +/- 0.20			DRAWING FILE : DRAWING\U10\U10BH74X2X01X-12				SIZE A3 U10BH74X2X01X				REV. 12	
FRACTIONS +/-												
ANGLES +/- 3°			ANGLE OF PROJECTION				SCALE NONE				SHEET 2 OF 2	
FOR MATERIALS AND FINISHES SEE NOTES												
REMOVE SHARP EDGES												
DIMENSIONS												
U.S. INCHES												
(METRIC) (MM)												