
Data sheet

WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Feed-through terminal block, Screw connection, dark beige, 6 mm², 41 A, 800 V, Number of connections: 2
Order No.	1887220000
Type	WTD 6/4 FF
GTIN (EAN)	4032248526802
Qty.	50 items

Downloaded from Arrow.com.

Data sheet

WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Dimensions and weights

Depth	52 mm	Depth (inches)	2.0472 inch
Depth including DIN rail	53.4 mm	Height	76.5 mm
Height (inches)	3.0118 inch	Width	11 mm
Width (inches)	0.4331 inch	Net weight	31.59 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection, for plug-in cross-connector, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Mounting rail	TS 35, TS 32	N-function	No
PE function	No	PEN function	No

Additional technical data

Explosion-tested version	No	Type of mounting	Snap-on

CSA rating data

Voltage size B (cCSAus)	600 V	Voltage size C (cCSAus)	600 V
Current size D (cCSAus)	40 A	Wire cross section min. (cCSAusX)	26 AWG
Current size C (cCSAus)	40 A	Certificate number (cCSAus)	227775-1609344
Wire cross section max. (cCSAusX)	10 AWG	Current size B (cCSAus)	40 A
Voltage size D (cCSAus)	600 V		

Downloaded from Arrow.com.

WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection

Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 10	Connection direction	on side
Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
Stripping length	8 mm	Type of connection	Screw connection
Number of connections	2	Clamping range, max.	6 mm²
Clamping range, min.	1.5 mm²	Clamping screw	M 4
Blade size	0.8 x 5.5 mm	Wire connection cross section AWG, min.	AWG 16
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1.5 mm²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm²
Wire connection cross section, finely stranded, max.	6 mm²	Wire connection cross section, finely stranded, min.	1.5 mm²
Connection cross-section, stranded, max.	6 mm²	Connection cross-section, stranded, min.	1.5 mm²
Wire connection cross-section, solid core, max.	10 mm²	Wire connection cross-section, solid core, min.	1.5 mm²
Connection cross-section, finely stranded, min.	1.5 mm²		

Dimensions

TS 32 offset	38.5 mm	TS 35 offset	38.5 mm

General

Wire connection cross section AWG, max.	AWG 10	Wire connection cross section AWG, min.	AWG 16
Standards	IEC 60947-7-1	Mounting rail	TS 35, TS 32

Rating data

Rated cross-section	6 mm²	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	41 A
Current at maximum wires	41 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.78 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	1.31 W	Pollution severity	3

UL rating data

Conductor size Factory wiring max. (cURus)	10 AWG	Voltage size B (cURus)	600 V
Certificate No. (cURus)	E60693	Conductor size Field wiring min. (cURus)	26 AWG
Conductor size Factory wiring min. (cURus)	26 AWG	Current size B (cURus)	30 A
Voltage size C (cURus)	600 V	Current size C (cURus)	30 A
Conductor size Field wiring max. (cURus)	10 AWG		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications


ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.