

**Part Number :** [936000221](#)

**Product Description :** Heavy-Duty EMC - Electromagnetic Compatibility Metal Cable Gland with Gasket, for 18.00-25.00mm Cable, Pg29 Thread

**Series Number :** 93600

**Status :** Active

**Product Category :** Heavy-Duty Cable Glands

**Engineering Part Number :** 7000.7346.0



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

---

## Part Details

### General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty EMC - Electromagnetic Compatibility Metal Cable Gland with Gasket, for 18.00-25.00mm Cable, Pg29 Thread
Cable Gland Type	IP68 - EMC
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	DIN 40430
UPC	887191843131

### Physical

Cable Diameter	18.00-25.00mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel
Net Weight	106.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg29
Thread Type	(Pg)

## Mates With / Use With

### Use with Part(s)

Description	Part Number
-------------	-------------

Use With	Where Electromagnetic Compatibility is required, industrial connectors, hoods, housings, sealed enclosures, and boxes
----------	---

---

This document was generated on Jun 02, 2026