


SIGN	DATE	DESCRIPTION	APPROVER
1	8/07'06	Added VDE standard	黎仁松
2	2008.12.02	The temperature changed from -30°c,+105°c to -40°c,+115°c	Jacke
3	2008.12.02	The dimension design changed from 19.1mm to 19.3mm	Jacke
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	







N = Number of contacts

Material

- Item ⓐ Clamp: Brass(CuZn),Nickel plated
- Item ⓑ Terminal screw: Steel Zinc plating "-" slot type
- Item ⓒ Female contact: PhBz, Tin plated
- Item ⓓ Terminal (housing): Thermoplastic (UL94V-0)
- Item ⓔ Terminal (cover): Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Wire range: 1.5mm²
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 1.7Lb-In./0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- ② Operating temperature: -40°C to +115°C
- ① Safety approval: cULus VDE

TS xx 1 1 x B xxxx G

No. OF POLES	Color	RoHS pb<40 , 000ppm
02: 2 POLES : : 24: 24 POLES	0 Black (RAL9005) 2 Red (RAL3001/D) 3 Orange(RAL2011/P) 4 Yellow(RAL1018/A) 5 Green(RAL6018/T) 6 Blue (RAL5015/A) 8 Grey(RAL7035/D)	0000 Standard @ Logo 000A Standard ANY Logo Any special item by customer request, please contact sales department.

DIMENSION

A	NX3.5
B	(N-1)X3.5

Poles	Tolerance
2P-8P	±0.10
9P-16P	±0.20
17P-24P	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TS-3.5mm Series Without flange (for latch on back side)				
PART NO.	TSxx11xBxxxxG			DWG NO.	8TS0202
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacke 2008.12.10	Jacke 2008.12.10	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: F	Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°

Downloaded from Arrow.com.