




Part Number : [2131910003](#)
Product Description : PowerPlane Busbar
Assembly, Large Size, Right-Angle, Screw Mount,
3.00mm and 3.18mm Bus Bar Thickness
Series Number : 213191
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[2131910003_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2131910001-AS-000.pdf](#)

[2131910001-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	213191
Description	PowerPlane Busbar Assembly, Large Size, Right-Angle, Screw Mount, 3.00mm and 3.18mm Bus Bar Thickness
Application	Power
Component Type	PCB Receptacle
Product Name	PowerPlane
UPC	195842410688

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	320.0A
Voltage - Maximum	1000V

Physical

Circuits (Loaded)	1
-------------------	---

Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Resin	Liquid Crystal Polymer
Net Weight	21.560/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw

This document was generated on Sep 24, 2025