



**Part Number :** [1200659533](#)  
**Product Description :** Micro-Change (M12)  
Single-Ended Cordset with Knurled Hexnut, 5  
Poles, Male (90°) to Pigtail, 22 AWG, Black TPU  
WSOR Cable, 10.0m (32.81') Length  
**Series Number :** 120065  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 805007B30M100



## Documents & Resources

**Drawings**  
[1200659533\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, Male (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	889056070867

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

### Physical

Cable Diameter	5.50mm (.216")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None

Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	795.000/g
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	22

---

This document was generated on Apr 22, 2025