


Data Sheet | Item Number: 787-1711

Switched-mode power supply; Eco; 1-phase; 12 VDC output voltage; 4 A output current; DC-OK LED

<https://www.wago.com/787-1711>



Similar to illustration

Features:

- Switched-mode power supply
- Natural convection cooling when horizontally mounted
- Encapsulated for use in control cabinets
- Suitable for both parallel and series operation
- Electrically isolated output voltage (SELV) per EN 60335-1; PELV per EN 60204
- DIN-35 rail mountable in different positions
- Direct installation on mounting plate via cable grip

Technical data

Input		Output	
Phases	1	Nominal output voltage $U_{o, nom}$	12 VDC (SELV)
Nominal input voltage $U_{i, nom}$	1 x 100 ... 240 VAC	Output voltage range	10 ... 14 VDC (adjustable)
Input voltage range	1 x 90 ... 264 VAC; 125 ... 375 VDC	Default Setting	12 VDC
Nominal mains frequency range	47 ... 63 Hz; 0 Hz	Nominal output current $I_{o, nom}$	4 A (12 VDC; 110 ... 240 VAC); 3.2 A (12 VDC; 100 ... 240 VAC)
Input current I_i	≤ 1.8 A (100 VAC)	Nominal output power	48 W
Discharge current	≤ 3.5 mA	Deviation	≤ 1 %
Inrush current	≤ 18 A	Residual ripple	≤ 150 mV (peak-to-peak)
Power factor correction (PFC)	Passive	Overload behavior	Constant power (in overload range: 1.05 ... 1.4 x $I_{o, nom}$); Shutdown and automatic restart in the event of a short circuit
Mains failure hold-up time	≥ 10 ms (230 VAC)		

Signaling and Communication

Signaling	1 x DC OK LED (green)
Operation status indicator	Green LED (U_o)

Efficiency/Power Losses

Power loss P_i	≤ 9.6 W (230 VAC; 12 VDC; 4 A)
Efficiency (typ.)	80 % (230 VAC; 4 ADC)

Circuit Protection

Internal fuse	F 2 A / 250 VAC
Pre-fuse (required)	An external DC fuse is required for the DC input voltage.
Backup fuse (recommended)	Circuit breaker: B6, B10

Safety and protection

Isolation voltage (pri.-sec.)	4.242 kVDC
Isolation voltage (pri.-PE)	2.2 kVDC
Isolation voltage (sec.-PE)	0.7 kVDC
Protection class	I
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ 14 VDC
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes, for 2 devices of the same type
MTBF	> 300,000 h (per IEC 61709)

Connection Data

Note (conductor cross-section)	12 AWG: THHN, THWN
Connection 1	
Connection type	Input/output
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 236 Series
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Strip length	6 ... 7 mm / 0.24 ... 0.28 inches

Physical data

Width	40 mm / 1.575 inches
Height	90 mm / 3.543 inches
Depth from upper-edge of DIN-rail	99 mm / 3.898 inches

Mechanical data

Mounting type	DIN-35 rail Screw mount
---------------	----------------------------

Material data

Fire load	0.123 MJ
Weight	250 g

Environmental requirements

Ambient temperature (operation)	-20 ... +60 °C
Ambient temperature (storage)	-25 ... +75 °C
Relative humidity	10 ... 95 % (no condensation permissible)
Derating	-4 %/K (> 45 °C)
Climatic category	3K3 (per EN 60721)

Standards and Specifications

Conformity marking	CE
Standards/specifications	EN 61204-3 EN 60335-1 EN 61558-2-6 EN 62368-1 SEMI F47

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143656030
Customs tariff number	85044083900

Product Classification

UNSPSC	39121004
eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 9.0	EC002540
ETIM 10.0	EC002540
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
SCIP notification number (Bulgaria)	ba9a4dde-70b7-46d5-918c-d2e3694d1c3f
SCIP notification number (Czech Republic)	d82ac068-d9b6-4461-8538-91ca53ecf9ae

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03078
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
MFD for SEMI F47 WAGO GmbH & Co. KG	-	-

Downloads

Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 787-1711			↓

Documentation

Bid Text			
787-1711	01.10.2019	xml 6.77 KB	↓
787-1711	25.11.2019	docx 17.40 KB	↓

Instruction Leaflet			
ECO Power Switched-Mode Power Supplies	V 1.4 21.12.2020	pdf 248.33 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 787-1711	↓

CAE data	
EPLAN Data Portal 787-1711	↓
ZUKEN Portal 787-1711	↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 210-831

Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white

Item No.: 210-832

Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Tool

1.1.2.1 Operating tool



Item No.: 210-720

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Item No.: 210-769

SCREWDRIVER; green

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com