



Technical Data

12.04.2021

Heat Shrinkable Tubing up to 3:1 - 1 m lengths
HU47 - thick wall unlined

HU47-13/4

Article Number 321-10130



Material:	Polyolefin, cross-linked (PO-X)	
Colour:	Black (BK)	
Shrink Ratio:	up to 4:1	
Longitudinal Change After Shrinkage:	-10 % max.	
Min. Shrink Temperature - °C:	+120 °C	
Flammability:	not flame retardant	Test Method
Operating Temperature - °C:	-55 °C to +110 °C, (outer wall only)	
Heat Shock Test:	4h/225°C	
Behaviour at Heat Shock:	not cracking, not fluid, not dripping	
Heat Aging Test:	168h/150°C	ASTM D2671
Minimum Tensile Strength At Heat Aging:	12 MPa	
Elongation At Heat Aging:	300 %	
Behaviour At Low Temperature:	not cracking	ASTM D2671
Dielectric Strength:	15 kV/mm	IEC 60243
Tensile Strength:	12 MPa	ASTM D2671
Elongation at break:	3.5	ASTM D2671
Water Absorption:	0.5 %	

HF✓

RoHS✓

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved