

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples



Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

Features

- Low Insertion Loss
- High Out of Band Attenuation
- SMD Mount

Applications

- GNSS, GPS, GLONASS, BeiDou Filter
- Navigational and Positioning applications
- GPS Receivers, Mobile Phones

Electrical Specifications

Parameters		Specifications		
		Min	Typ	Max
Nominal Center Frequency (Fc) (MHz)			1582.47	
Insertion Loss (dB)	1574.42 ~ 1576.42 MHz		1.2	1.7
	1597.55 ~ 1605.89 MHz		2.0	2.5
	1559.05 ~ 1563.14 MHz		1.7	2.5
Amplitude Ripple (dB _{p-p})	1574.42 ~ 1576.42 MHz		0.1	0.8
	1597.55 ~ 1605.89 MHz		0.55	1.4
	1559.05 ~ 1563.14 MHz		0.2	1.2
Group Delay Ripple (nsec)	1574.42 ~ 1576.42 MHz		1.0	6.0
	1597.55 ~ 1605.89 MHz		6.0	12.5
	1559.05 ~ 1563.14 MHz		5.0	16.0
VSWR	1574.42 ~ 1576.42 MHz		1.5	2.1
	1597.55 ~ 1605.89 MHz		1.4	2.0
	1559.05 ~ 1563.14 MHz		1.5	2.0
Attenuation (dB) (Reference level from 0dB)	699 ~ 716 MHz	37	42	
	777 ~ 787 MHz	37	42	
	814 ~ 849 MHz	37	42	
	880 ~ 915 MHz	37	42	
	1427.9 ~ 1446.9 MHz	43	48	
	1447.9 ~ 1462.9 MHz	45	50	
	1710 ~ 1785 MHz	40	47	
	1850 ~ 1915 MHz	40	46	
	1920 ~ 1980 MHz	40	46	
	2400 ~ 2500 MHz	37	42	
	2500 ~ 2570 MHz	37	42	
Terminating Source & Load Impedance (Ω)			50	
Maximum Input Power (dBm)				15
DC Voltage (V)				3



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples



Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3


Mechanical Specifications

Parameters	Specifications
Filter Dimension	1.1 x 0.9 x 0.55 mm
Mounting Type	SMD Mount

Environmental Specifications

Parameters	Specifications
Operating Temperature Range	-30°C ~ +85°C
Storage Temperature Range	-40°C ~ +85°C
MSL level	3
ESD	50V (MM), 100V (HBM)

Package Dimensions



Pin No.	Symbol	Function
A	IN	Input
B	GND	Ground
C	GND	Ground
D	OUT	Output
E	GND	Ground

All tolerances are +/-0.1 mm unless otherwise specified.
Unit: mm

Marking Description

: Year/Month Code (Follow the table)

YEAR/Month	1	2	3	4	5	6	7	8	9	10	11	12
2019	<u>a</u>	<u>b</u>	<u>c</u>	<u>d</u>	<u>e</u>	<u>f</u>	<u>g</u>	<u>h</u>	<u>i</u>	<u>k</u>	<u>l</u>	<u>m</u>
2020	<u>n</u>	<u>p</u>	<u>q</u>	<u>r</u>	<u>s</u>	<u>t</u>	<u>u</u>	<u>v</u>	<u>w</u>	<u>x</u>	<u>y</u>	<u>z</u>
2021	A	B	C	D	E	F	G	H	J	K	L	M
2022	N	P	Q	R	S	T	U	V	W	X	Y	Z
2023	a	b	c	d	e	f	g	h	j	k	l	m
2024	n	p	q	r	s	t	u	v	w	x	y	z
2025	<u>A</u>	<u>B</u>	<u>C</u>	<u>D</u>	<u>E</u>	<u>F</u>	<u>G</u>	<u>H</u>	<u>J</u>	<u>K</u>	<u>L</u>	<u>M</u>
2026	<u>N</u>	<u>P</u>	<u>Q</u>	<u>R</u>	<u>S</u>	<u>T</u>	<u>U</u>	<u>V</u>	<u>W</u>	<u>X</u>	<u>Y</u>	<u>Z</u>



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory




1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

PCB Footprint



Measurement Circuit



1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

Transmission Characteristics

S21 Response (Narrowband)



1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM


Request Samples



Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

S21 Response (Wideband)



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

Group Delay Ripple



1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory





1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

Reflection Characteristics

S11 & S22 VSWR



S11 & S22 Smith Chart



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED

1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples




Check Inventory



1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3

Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds minimum.
3. Heating shall be fixed at 220°C for 50~80seconds and at 260°C+0/-5°C peak (20~40sec)
4. Time: 2 times



1582.47 MHz SMD SAW Filter

ABSTS5A2-2HMM01MM

Request Samples



Check Inventory




1.1 x 0.9 x 0.55 mm
RoHS/RoHS II Compliant
MSL Level = 3


Packaging

1. Reel Dimension

Number of pieces/reel: 5k



2. Tape Dimension



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent medical applications, or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 06-03-21

ABRACON IS
ISO9001-2015
CERTIFIED