





PRODUCT NUMBER	PITCH
KRxx01x000J0G	5.00 mm



Material

- Item ① Clamp: Brass(CuZn) Ni plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: PhBz (CuSn) Tin plated
- Item ④ Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 14-26
- Stranded wire(AWG): 14-26
- Torque: 3.5Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

PART NO.: KR xx 01 x 0 00J0 G

N = Number of poles

Dim A=Nx5.0

Dim B=(N-1)x5.0

poles	Tolerance	Dim C	Dim D
2P	±0.05	≤0.05	≤0.05
3-6p	±0.15	≤0.10	≤0.10
7-12p	±0.20	≤0.20	≤0.20
13-18p	±0.30	≤0.20	≤0.20
19-24p	±0.40	≤0.40	≤0.40

Solid block	No. of poles	Body Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	0 Black (RAL9005)	
03	3 poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
24	24 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK											
ltr ecn no dr date				tolerances unless otherwise specified								title TERMINAL BLOCK									
				linear angles		X.±0.5						PLUGGABLE,180D WIRE INLET,SOLID BLOCK,WITHOUT HOOK									
						X.X±0.3															
						X.XX±0.1															
				X*±1°						scale		dwg no									