


© – TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K1	ECR-25-239014	11NOV2025	ABS	PS







SECTION X–X



RECOMMENDED HOLE LAYOUT

11	6	8	9	7	16	48.77 [1.920]	50.67 [1.995]	18	19	5-147969-5
11		8	9	7	17	48.77 [1.920]	50.67 [1.995]	18	19	5-147969-4
11		8	9	7	10	28.45 [1.120]	30.35 [1.195]	10	11	5-147969-3
11		8	9	7	19	51.31 [2.020]	53.21 [2.095]	19	20	5-147969-2
		8	9	7	2	8.13 [.320]	10.03 [.395]	2	3	5-147969-1
11	6	8		1	18	51.31 [2.020]	53.21 [2.095]	19	20	147969-6
11	6	8		1	16	48.77 [1.920]	50.67 [1.995]	18	19	147969-5
		8		1	17	48.77 [1.920]	50.67 [1.995]	18	19	147969-4
11		8		1	10	28.45 [1.120]	30.35 [1.195]	10	11	147969-3
11		8		1	19	51.31 [2.020]	53.21 [2.095]	19	20	147969-2
SUPERSEDED BY 5-147969-1		8		1	2	8.13 [.320]	10.03 [.395]	2	3	147969-1
		REMARKS		PLATING	POSITIONS OMITTED	C	B	A	NO. OF POSN	PART NO.

1 .00254[.000100] BRIGHT TIN–LEAD OVER .00127[.000050] NICKEL.

2 POINT OF MEASUREMENT FOR PLATING THICKNESS.

3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.

4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.

5 POSITION NOTED FOR REFERENCE ONLY.

6 PRELIMINARY PART–NOT RELEASED FOR PRODUCTION.

7 .00254[.000100] MATTE TIN OVER .00127[.000050] NICKEL.

8 HIGH TEMPERATURE CONFIGURATION

9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY

10 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

11 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13[.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL HOUSING: FLAME RETARDANT LCP, COLOR–BLACK
CONTACTS:BRASS

FINISH SEE TABLE

DWN	R.BROWN	10SEP01
CHK	K.WRIGHT	10SEP01
APVD	K.WRIGHT	10SEP01
PRODUCT SPEC	108-25034	
APPLICATION SPEC	114-25026	
WEIGHT	–	

TE Connectivity

NAME
HDR ASSY, VERT, SINGLE ROW
2.54[.100] CL, 0.64[.025] SQ POST,
WITH PLZN & LATCHING, AMPMODU MTE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-147969	–

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV K1

147969

1471-9 (1/15)

Downloaded from Arrow.com.