



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JUN-20-2014	BEN	TOMMY
B2	-	UPDATE RATED VOLTAGE	JUL-10-2023	JUN	TOMMY







NOTES: (UNLESS OTHERWISE SPECIFIED)
1. MATERIAL:
   SHELL: ZINC ALLOY, NICKEL PLATED.
   INSERT: THERMOPLASTIC, UL94 V-0.
   SEAL GASKET: NBR/SILICONE RUBBER.
   O-RING: NBR/SILICONE RUBBER.
2. SPECIFICATIONS:
   2.1 RATED CURRENT: 45A (MAX).
   2.2 RATED VOLTAGE: 600V (AC/DC) .
   2.3 OPERATING TEMPERATURE: SEE CHART.
   2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@2000 VOLTS AC.
   2.5 INSULATION RESISTANCE: 5000 MEGOHMS MIN.
   2.6 IP--CLASS: IP67.
   2.7 MATING CYCLES DURABILITY: 500 CYCLES MIN.
   2.8 ROHS COMPLIANT.
3. SUITABLE CONTACTS : 8# CONTACTS.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



PANEL CUT OUT REFERENCE

KEY POS	PART NUMBER	
	-40°C ~ 105°C	-40°C ~ 125°C
N	RT00164PNH	RT00164PNH03
W	RT00164PWH	RT00164PWH03
X	RT00164PXH	RT00164PXH03
Y	RT00164PYH	RT00164PYH03
Z	RT00164PZH	RT00164PZH03

	SEE PART NUMBER CHART		
QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30 | Fractions ±1/64
2 PL DEC ±0.15 | Angles ±1°
3 PL DEC ±0.08
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		DATE
DRAWN:	JUN	JUL-10-2023
CHECKED:	JOE	JUL-12-2023
ENGINEER:		
APPROVAL:	TOMMY	JUL-14-2023
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ECO-MATE,RECEPTACLE,
SIZE 16,4POS,PIN.

SIZE	TYPE	DWG NO:	REVISION
B	C-	RT00164P*H*	B2

SCALE: NONE SHEET 1 OF 1

TITLE: ECO-MATE,RECEPTACLE,SIZE 16,4POS,PIN.
DWG NO: RT00164P*H*
REV: B2
SH: 1
OF: 1

Downloaded from Arrow.com.

ecomate® RM/RSSM/Aquarius™ - Contact Size 3.6mm (1604 Insert Arrangement) Options

Crimp Contacts, 1604 Insert Arrangement, Machined					
Part Number		AWG	Wire Range (mm²)	For Use w Endcap	Plating
Male	Female				
MP10A23T	MS10A23T	12-10	3.0 - 6.0	Yes	Tin
MP10A23S	MS10A23S	12-10	3.0 - 6.0	Yes	Silver
MP10A23F	MS10A23F	12-10	3.0 - 6.0	Yes	Gold Flash
MP10A23G5	MS10A23G5	12-10	3.0 - 6.0	Yes	Gold 5µ"
MP10S23G10	MS10A23G10	12-10	3.0 - 6.0	Yes	Gold 10µ"
MP10A23G15	MS10A23G15	12-10	3.0 - 6.0	Yes	Gold 15µ"
MS10A23G30	MS10A23G30	12-10	3.0 - 6.0	Yes	Gold 30µ"

Tooling, Machined	
Part Number	Description
QXRT08	Contact Extraction Tool, # 8 (Ø 3.6mm) Contact
M300BT	Hand Crimper
WA27-300BT-EP	Pneumatic Crimper
TP968	Locator M3200BT and WA27-300BT-EP

Plating Options	
Symbol	Plating
T	Tin Plating Over Nickel
S	Silver Plating Over Nickel
F	Gold Plated
G5	Gold Plated (Thickeness 5µ")
G10	Gold Plated (Thickeness 10µ")
G15	Gold Plated (Thickeness 15µ")
G30	Gold Plated (Thickeness 30µ")

Downloaded from Arrow.com.