

- High power density 25W converter
Ultra compact design: 1.0" x 1.0" x 0.4"
- Shielded metal case with isolated baseplate
- Wide 2:1 input voltage ranges
- Very high efficiency up to 90%
- Output voltage adjustable
- Remote On/Off control
- Operating temp. range -40°C to $+80^{\circ}\text{C}$
and up to $+85^{\circ}\text{C}$ with heat-sink
- I/O isolation voltage 1500 VDC
- 3-year product warranty



UL 62368-1 IEC 62368-1

The THL 25 series is a generation of DC-DC converter modules with high power density. The product achieves 25 Watt output power and comes in a metal case with small dimensions of only 1.0"x 1.0"x 0.4". All models have a wide 2:1 input voltage range and precisely regulated output voltages. High efficiency of up to 90% makes this product very reliable and applicable in temperature ranges of up to $+80^{\circ}\text{C}$ or up to $+85^{\circ}\text{C}$ with optional mounted heat sink. Typical applications are in mobile equipments, instrumentation, distributed power architectures in communication and industrial electronics and everywhere where space on the PCB is critical

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
THL 25-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	6'000 mA			87 %
THL 25-1211		5 VDC	5'000 mA			89 %
THL 25-1212		12 VDC	2'090 mA			89 %
THL 25-1213		15 VDC	1'670 mA			89 %
THL 25-1222		+12 VDC	1'040 mA	-12 VDC	1'040 mA	89 %
THL 25-1223		+15 VDC	840 mA	-15 VDC	840 mA	89 %
THL 25-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	6'000 mA			88 %
THL 25-2411		5 VDC	5'000 mA			90 %
THL 25-2412		12 VDC	2'090 mA			90 %
THL 25-2413		15 VDC	1'670 mA			90 %
THL 25-2422		+12 VDC	1'040 mA	-12 VDC	1'040 mA	89 %
THL 25-2423		+15 VDC	840 mA	-15 VDC	840 mA	89 %
THL 25-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	6'000 mA			88 %
THL 25-4811		5 VDC	5'000 mA			90 %
THL 25-4812		12 VDC	2'090 mA			90 %
THL 25-4813		15 VDC	1'670 mA			90 %
THL 25-4822		+12 VDC	1'040 mA	-12 VDC	1'040 mA	89 %
THL 25-4823		+15 VDC	840 mA	-15 VDC	840 mA	89 %

Options

THL-HS1	- Optional Heat Sink: www.tracopower.com/overview/thl-hs1
---------	--

Input Specifications

Input Current	- At no load	12 Vin models: 80 mA typ. 24 Vin models: 55 mA typ. 48 Vin models: 40 mA typ.
	- At full load	12 Vin models: 1'900 mA typ. (3.3 Vout model) 2'350 mA typ. (5 Vout model) 2'350 mA typ. (12 Vout model) 2'350 mA typ. (15 Vout model) 2'350 mA typ. (12 / -12 Vout model) 2'350 mA typ. (15 / -15 Vout model) 24 Vin models: 950 mA typ. (3.3 Vout model) 1'150 mA typ. (5 Vout model) 1'150 mA typ. (12 Vout model) 1'150 mA typ. (15 Vout model) 1'150 mA typ. (12 / -12 Vout model) 1'150 mA typ. (15 / -15 Vout model) 48 Vin models: 450 mA typ. (3.3 Vout model) 580 mA typ. (5 Vout model) 580 mA typ. (12 Vout model) 580 mA typ. (15 Vout model) 580 mA typ. (12 / -12 Vout model) 580 mA typ. (15 / -15 Vout model)
Surge Voltage		12 Vin models: 25 VDC max. (100 ms max.) 24 Vin models: 50 VDC max. (100 ms max.) 48 Vin models: 100 VDC max. (100 ms max.)
Reflected Ripple Current		12 Vin models: 80 mAp-p typ. 24 Vin models: 50 mAp-p typ. 48 Vin models: 30 mAp-p typ.
Recommended Input Fuse		12 Vin models: 5'000 mA (slow blow) 24 Vin models: 2'500 mA (slow blow) 48 Vin models: 1'250 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal LC-Type

Output Specifications

Output Voltage Adjustment		±10% (single output models only) (By external trim resistor) See application note: www.tracopower.com/thl25-adj/ Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.2% max. dual output models: 0.2% max.
	- Load Variation (0 - 100%)	single output models: 0.2% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
	- Voltage Balance (symmetrical load)	dual output models: 2% max.
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Ripple and Noise (20 MHz Bandwidth)	- single output	3.3 Vout models:	100 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
		5 Vout models:	100 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
		12 Vout models:	150 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
		15 Vout models:	150 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
	- dual output	12 / -12 Vout models:	150 / 150 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
		15 / -15 Vout models:	150 / 150 mVp-p max. (w/ 1 μ F MLCC 10 μ F Tantalum)
Capacitive Load	- single output	3.3 Vout models:	10'300 μ F max.
		5 Vout models:	6'800 μ F max.
		12 Vout models:	1'200 μ F max.
		15 Vout models:	750 μ F max.
	- dual output	12 / -12 Vout models:	680 / 680 μ F max.
		15 / -15 Vout models:	380 / 380 μ F max.
Minimum Load	Not required		
Temperature Coefficient	± 0.02 %/K max.		
Start-up Time	30 ms max. (Power On) 30 ms max. (Remote On)		
Short Circuit Protection	Continuous, Automatic recovery		
Output Current Limitation	150% typ. of Iout max.		
Overvoltage Protection	118 - 125% of Vout nom. (depending on model) 3.9 VDC typ. (3.3 Vout models) 6.2 VDC typ. (5.1 Vout models) 15 VDC typ. (12 Vout models) 18 VDC typ. (15 Vout models)		
Transient Response	- Response Deviation	3% typ. / 5% max. (75% to 100% Load Step)	
	- Response Time	250 μ s typ. (75% to 100% Load Step)	

Safety Specifications

Standards	- IT / Multimedia Equipment	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Certification Documents	www.tracopower.com/thl25-safety-cert/
Energy Source	- Output, acc. to 62368-1	ES1
Power Source	- Output, acc. to 62368-1	PS3
Over Voltage Category		Not mains connected

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter)
External filter proposal:		www.tracopower.com/thl25-emc-filter/

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMS (Immunity)	- Electrostatic Discharge	EN 55024 (IT Equipment)
	- RF Electromagnetic Field	EN 55035 (Multimedia)
	- EFT (Burst) / Surge	Air: EN 61000-4-2, ± 8 kV, perf. criteria A
	- Conducted RF Disturbances	Contact: EN 61000-4-2, ± 6 kV, perf. criteria A
	- PF Magnetic Field	EN 61000-4-3, 10 V/m, perf. criteria A
	- Certification Documents	EN 61000-4-4, ± 2 kV, perf. criteria A
		EN 61000-4-5, ± 1 kV, perf. criteria A
		Ext. input component: KY 220 μ F, 100 V, ESR 48 mOhm
EMC / Environmental		Continuous: EN 61000-4-6, 10 Vrms, perf. criteria A
		EN 61000-4-8, 3 A/m, perf. criteria A
		www.tracopower.com/thl25-emc-cert/

General Specifications		
Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +80°C
	- Case Temperature	-40°C to +85°C (with heatsink THL-HS1)
	- Storage Temperature	+105°C max.
Power Derating	- High Temperature	-50°C to +125°C
		Depending on model
Cooling System		See application note: www.tracopower.com/thl25-cc/
Remote Control	- Voltage Controlled Remote (passive = on)	Natural convection (20 LFM)
	- Off Idle Input Current	On: 3.5 to 12 VDC or open circuit
	- Remote Pin Input Current	Off: 0 to 1.2 VDC or short circuit
Altitude During Operation		Refers to 'Remote' and '-Vin' Pin
Switching Frequency		3 mA typ.
Insulation System		-0.5 to 0.5 mA
Isolation Test Voltage	- Input to Output, 60 s	6'000 m max.
	- Input to Output, 1 s	285 kHz typ. (PWM)
Isolation Resistance	- Input to Output, 500 VDC	Functional Insulation
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	1'500 VDC
Reliability	- Calculated MTBF	1'800 VDC
Washing Process		1'000 M Ω min.
Housing Material		2'000 pF max.
Base Material		313'000 h (MIL-HDBK-217F, ground benign)
Potting Material		According to Cleaning Guideline
Pin Material		www.tracopower.com/info/cleaning.pdf
Pin Foundation Plating		Alu alloy, black anodized coating
Pin Surface Plating		Non-conductive FR4 (UL 94 V-0 rated)
Housing Type		Epoxy (UL 94 V-0 rated)
Mounting Type		Copper Alloy (C6801)
Connection Type		Nickel (2.5 μ m min.)
Footprint Type		Gold (75 - 125 nm), glossy
Soldering Profile		Metal Case
Weight		PCB Mount
Thermal Impedance	- Case to Ambient	THD (Through-Hole Device)
		1" x 1"
		Lead-Free Wave Soldering
		260°C / 10 s max.
		16.5 g
		17.6 K/W typ.
		14.8 K/W typ. (with heatsink THL-HS1)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7(a)

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)

- SCIP Reference Number

417b0817-1715-4eb8-b5e7-d3a799dc1fad

Additional Information

Supporting Documents

www.tracopower.com/overview/thl25

Frequently Asked Questions

www.tracopower.com/glossary-faq


Glossary

www.tracopower.com/info/glossary.pdf

Service Portal

www.tracoserviceportal.com

Outline Dimensions



Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	
2	-Vin (GND)	
3	+Vout	
4	Trim	Common
5	-Vout	
6	Remote On/Off	

Avoid routing PCB traces under the converter.

Dimensions in mm (inch)

Tolerances: x.x ±0.5 (x.xx ±0.02)

x.xx ± 0.25 (x.xxx ±0.010)

Pin tolerances: x.x ±0.05 (x.xx ±0.002)

