




## CNX714 Series 0.551" (14mm) Ruggedized LED Panel Mount Indicator



Ruggedized CNX714 Series with built-in LED offers fast, easy installation in harsh environments.



### Applications

- Industrial Machinery
- Transportation Dashboards
- Instrument Panels
- Control Cabinets
- Safety Applications
- Disinfection and Sterilization
- Switching Stations
- Slot, Gaming and Vending Machines
- Outdoor Signs
- Military Aircraft

### Key Features

- For panel hole diameter: 0.551" (14mm)
- Designed for extreme harsh and outdoor environments.
- Variety of connection options for fast, easy installation.
- Built-in LED can be used with FlexVolt™ (5 to 28 VDC) or 120VAC circuits
- Fast pitch threads ease assembly, requiring only one turn.
- Nut assembly by finger-tightening or with 1 inch hex key.
- Outdoor visibility in direct sunlight.
- Available in six solid colors (red, green, white, blue, soft yellow and yellow).
- Wide Viewing Angle
- Resistant to shock and vibration.
- Moisture sealed, IP67, protected from total dust ingress and withstanding water immersion between 15 cm and 1 meter for 30 minutes.
- Lead wire options with custom wire length available.
- Other colors (single or bicolor) are available upon request.
- RoHS and REACH Compliant.

## Ordering Data

The CNX714 Series is available in a range of standard features and options. To specify your Panel Mount Indicator, select one option from each column.


LED Color		Voltage	Termination Style	
CNX714C			W	
CNX714C: Colored Body				
200	Red		W	
400*	Soft Yellow		Wire Leads	
401	Yellow			
500	Green			
600	Blue			
900	White			
FV	5-28VDC			
120	120VAC			

Example:  
CNX714C600120W  
Blue  
120VAC  
Wire Leads




\* Not Available for the 120VAC Version

## Product Dimensions



Recommended Mounting Hole



All Dimensions in inches [mm]

Tolerances are:  $\pm 0.01$  inches [ $\pm 0.25$  mm] unless otherwise specified

## Product Specifications

### Flex Voltage Version:

LED output		
LED color	Luminous intensity typ. (mcd)	I (mA)
red	1300-2700	20
soft yellow	80-400	20
yellow	450-1120	20
green	1000-1400	20
blue	280-710	20
white	1300-1800	20

### 120VAC Version:

LED output		
LED color	Luminous intensity typ. (mcd)	I (mA)
red	550	8
yellow	245	8
green	924	8
blue	67	8
white	644	8

### Installation Specification

mounting hole	0.551" (14.0mm)
panel thickness	Up to .250" (6.3mm)
spacing	minimum 1.5" center to center
retainer width	1" (25.4 mm)

### Temperatures

operating temperature	-40°F (-40°C) to 176°F (80°C)
storage temperature	-40°F (-40°C) to 212°F (100°C)

### Materials

body	polycarbonate, UL94-V2
retaining nut	PBT/Glass Filled, UL94-V0
wire	24 AWG - Black/Red** 20 AWG - Black***
lens	polycarbonate, UL94-V2
moisture seal	EPDM

\*\* Flex Voltage Version

\*\*\* 120 VAC Version

## Compliance and Approvals

