




MOUNTING HOLES



Directive 2002/95/EC RoHS compliant

Part no.	Finish Pos.1	Finish Pos.2 / 3	Finish Pos.4	Finish Pos.5
132A35029X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
132J35029X	min. 50µin HARD GOLD over min. 50µin NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	min. 30µin HARD GOLD over min. 50µin NICKEL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 7:1			
				material: COPPER ALLOY (Pos. 1 - 5)			title: COAXIAL CONTACT SOCKET 75 OHM Solder termination 90° with 3 pins for D-SUB Combination			
					date	name			dwg no:	DIN-A3 sh: 1
					drawn	29.01.14 Schmidt				
					appd.	31.01.14 Koch				
		norm			part no: see table					
		d-old								
a	Original									
rev.	description			date	name					