

REVISIONS

LTR	DESCRIPTION	DATE (YR-MO-DA)	APPROVED
D	Add vendor CAGE 34371. Add device type 02. Delete vendors CAGE 07263 and 31019. Change drawing CAGE code to 67268. Technical changes to 1.3, 1.4, table I , and table II - mbk.	90-03-30	Monica L. Poelking
E	Update boilerplate to MIL-PRF-38535 requirements. - jak	01-05-07	Thomas M. Hess
F	Made change to paragraph 3.5. Update boilerplate to MIL-PRF-38535 requirements. - LTG	05-02-09	Thomas M. Hess

FIRST PAGE OF THIS DRAWING HAS BEEN CHANGED.

CURRENT CAGE CODE 67268

REV																			
SHEET																			
REV																			
SHEET																			
REV STATUS OF SHEETS				REV	F	F	F	F	F	F	F	F	F	F	F				
				SHEET	1	2	3	4	5	6	7	8	9	10	11				
PMIC N/A				PREPARED BY A. J. Foley				DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990 http://www.dscc.dla.mil											
STANDARD MICROCIRCUIT DRAWING				CHECKED BY C. R. Jackson															
THIS DRAWING IS AVAILABLE FOR USE BY ALL DEPARTMENTS AND AGENCIES OF THE DEPARTMENT OF DEFENSE AMSC N/A				APPROVED BY Nelson A. Hauck				MICROCIRCUIT, DIGITAL, CMOS, QUAD 2-INPUT NAND GATE WITH SCHMITT TRIGGERS, MONOLITHIC SILICON											
				DRAWING APPROVAL DATE 77-10-06															
				REVISION LEVEL F				SIZE A	CAGE CODE 14933	77046									
								SHEET	1 OF 11										

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.
MIL-STD-1835 - Interface Standard Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.
MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at <http://assist.daps.dla.mil/quicksearch/> or <http://assist.daps.dla.mil> or from the Standardization Document Order Desk, 700 Robbins Avenue, Building 4D, Philadelphia, PA 19111-5094.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.

3.2.1 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 1.

3.2.3 Truth table. The truth table shall be as specified on figure 2.

3.2.4 Logic diagram. The logic diagram shall be as specified on figure 3.

3.2.5 Switching waveforms and test circuit. The switching waveforms and test circuit shall be as specified on figure 4.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 3

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full case operating temperature range.

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.

3.5 Marking. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked as listed in MIL-HDBK-103 (see 6.6 herein).

3.5.1 Certification/compliance mark. A compliance indicator "C" shall be marked on all non-JAN devices built in compliance to MIL-PRF-38535, appendix A. The compliance indicator "C" shall be replaced with a "Q" or "QML" certification mark in accordance with MIL-PRF-38535 to identify when the QML flow option is used.

3.6 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DSCC-VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.

3.7 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.

3.8 Notification of change. Notification of change to DSCC-VA shall be required in accordance with MIL-PRF-38535, appendix A.

3.9 Verification and review. DSCC, DSCC's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 4

TABLE I. Electrical performance characteristics.

Test	Symbol	Test conditions -55°C ≤ T _C ≤ +125°C unless otherwise specified		Device type	Group A subgroups	Limits		Unit
						Min	Max	
Quiescent supply current	I _{DD}	V _{IN} = 0.0 V or V _{DD}	V _{DD} = 5.0 V <u>1</u> /	All	1, 3		1.0	μA
					2		30.0	
			V _{DD} = 10.0 V <u>1</u> /	All	1, 3		2.0	
					2		60.0	
			V _{DD} = 15.0 V <u>1</u> /	All	1, 3		4.0	
					2		120.0	
Low-level output voltage	V _{OL}	V _{IN} = 0.0 V or V _{DD} I _O < 1 μA	V _{DD} = 5.0 V <u>3</u> /	All	1, 2, 3		0.05	V
			V _{DD} = 10.0 V <u>3</u> /	All	1, 2, 3		0.05	
			V _{DD} = 15.0 V	All	1, 2, 3		0.05	
High-level output voltage	V _{OH}	V _{IN} = 0.0 V or V _{DD} I _O < 1 μA	V _{DD} = 5.0 V <u>3</u> /	All	1, 2, 3	4.95		V
			V _{DD} = 10.0 V <u>3</u> /	All	1, 2, 3	9.95		
			V _{DD} = 15.0 V	All	1, 2, 3	14.95		
High-level output current	I _{OH}	V _{DD} = 5.0 V V _O = 4.6 V V _{IN} = 0.0 V or V _{DD}		All	1	-0.51		mA
					2	-0.36		
					3	-0.64		
		V _{DD} = 5.0 V V _O = 2.5 V V _{IN} = 0.0 V or V _{DD}		02	1	-1.6		
					2	-1.15		
					3	-2.0		
		V _{DD} = 10.0 V <u>3</u> /		All	1	-1.3		
					2	-0.9		
					3	-1.6		
Low-level output current	I _{OL}	V _{DD} = 5.0 V V _O = 0.4 V V _{IN} = 0.0 V or V _{DD}		All	1	0.51		mA
					2	0.36		
					3	0.64		
		V _{DD} = 10.0 V <u>3</u> /		All	1	1.3		
					2	0.9		
					3	1.6		
		V _{DD} = 15.0 V <u>3</u> /		All	1	3.4		
					2	2.4		
					3	4.2		

See footnotes at end of table.

**STANDARD
MICROCIRCUIT DRAWING**

DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
F

77046

SHEET
5

TABLE I. Electrical performance characteristics - Continued.

Test	Symbol	Test conditions -55°C ≤ T _C ≤ +125°C unless otherwise specified		Device type	Group A subgroups	Limits		Unit
						Min	Max	
Input current	I _{IN}	V _{DD} = 15.0 V V _{IN} = 0.0 V or V _{DD}	01	1, 3		±0.1		μA
				2		±1.0		
		V _{DD} = 20.0 V 2/ V _{IN} = 0.0 V or V _{DD}	02	1, 3		±0.1		
				2		±1.0		
Positive trigger threshold voltage	V _{T+}	V _{DD} = 5.0 V V _O = 0.5 V I _O < 1 μA	All	1, 2, 3	2.2	3.65		V
		V _{DD} = 10.0 V V _O = 1.0 V I _O < 1 μA	All	1, 2, 3	4.6	7.15		
		V _{DD} = 15.0 V V _O = 1.5 V I _O < 1 μA	All	1, 2, 3	6.8	10.8		
Negative trigger threshold voltage	V _{T-}	V _{DD} = 5.0 V V _O = 4.5 V I _O < 1 μA	All	1, 2, 3	0.9	2.80		V
		V _{DD} = 10.0 V V _O = 9.0 V I _O < 1 μA	All	1, 2, 3	2.5	5.20		
		V _{DD} = 15.0 V V _O = 13.5 V I _O < 1 μA	All	1, 2, 3	4.0	7.40		
Input capacitance	C _{IN}	V _{IN} = 0.0 V, T _C = +25°C, See 4.3.1c		All	4		7.5	pF
Functional tests		See 4.3.1d		All	7, 8			
Propagation delay time	t _{PHL} , t _{PLH}	C _L = 50 pF R _L = 200 kΩ t _r = t _f = 20 ns See figure 4	V _{DD} = 5.0 V	01	9	1.5	600.0	ns
					10, 11	1.5	840.0	
				02	9	1.5	380.0	
					10, 11	1.5	494.0	
			V _{DD} = 10.0 V	01	9	1.5	300.0	
					10, 11	1.5	420.0	
				02	9	1.5	180.0	
					10, 11	1.5	234.0	
			V _{DD} = 15.0 V	01	9	1.5	240.0	
					10, 11	1.5	335.0	
				02	9	1.5	130.0	
					10, 11	1.5	169.0	

See footnotes at end of table.

**STANDARD
MICROCIRCUIT DRAWING**

DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
F

77046

SHEET
6

TABLE I. Electrical performance characteristics – Continued.

Test	Symbol	Test conditions -55°C ≤ T _C ≤ +125°C unless otherwise specified		Device type	Group A subgroups	Limits		Unit
						Min	Max	
Transition time	t _{THL} , t _{TLH}	C _L = 50 pF R _L = 200 kΩ t _r = t _f = 20 ns See figure 4	V _{DD} = 5.0 V	01	9	1.5	200.0	ns
					10, 11	1.5	300.0	
				02	9	1.5	200.0	
					10, 11	1.5	260.0	
			V _{DD} = 10.0 V	02	9	1.5	100.0	
					10, 11	1.5	130.0	
			V _{DD} = 15.0 V	02	9	1.5	80.0	
					10, 11	1.5	104.0	

1/ For device type 02, this parameter is guaranteed, if not tested, to the specified limits in table I.

2/ This test is performed with V_{DD} = 18 V at T_C = -55 °C.

3/ This parameter is guaranteed, if not tested, to the specified limits in table I.

**STANDARD
MICROCIRCUIT DRAWING**
DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
F

77046

SHEET
7

Device types	All
Case outlines	C, D
Terminal number	Terminal symbol
1	1A
2	1B
3	1Y
4	2Y
5	2A
6	2B
7	V _{SS}
8	3A
9	3B
10	3Y
11	4Y
12	4A
13	4B
14	V _{DD}

FIGURE 1. Terminal connections.

(Each gate)

Inputs		Output
A	B	Y
L	L	H
L	H	H
H	L	H
H	H	L

H = High voltage level

L = Low voltage level

FIGURE 2. Truth table.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 8






FIGURE 3. Logic diagram.



NOTES:

1. $R_L = 200 \text{ k}\Omega$
2. $C_L = 50 \text{ pF}$, includes probe and jig capacitance.

FIGURE 4. Switching waveforms and test circuit.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 9

4. VERIFICATION

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.

4.2 Screening. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:

- a. Burn-in test, method 1015 of MIL-STD-883.
 - (1) Test condition A, B, C, or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
- b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.

4.3.1 Group A inspection.

- a. Tests shall be as specified in table II herein.
- b. Subgroups 5 and 6 in table I, method 5005 of MIL-STD-883 shall be omitted.
- c. Subgroup 4 (C_{IN} measurement) shall be measured only for the initial test and after process or design changes which may affect input capacitance. Capacitance shall be measured between the designated terminal and V_{SS} at a frequency of 1 MHz. Test all applicable pins on 5 devices with zero failures.
- d. Subgroups 7 and 8 shall include verification of the truth table as specified on figure 2.

4.3.2 Groups C and D inspections.

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition A, B, C, and D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 10

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	- - -
Final electrical test parameters (method 5004)	1, 2, 3, 7, 8, 9 <u>1/</u>
Group A test requirements (method 5005)	1, 2, 3, 4, 7, 8, 9, 10, 11 <u>2/</u>
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3

1/ PDA applies to subgroup 1.

2/ Subgroups 10 and 11, if not tested, shall be guaranteed to the specified limits in table I.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal.

6.4 Record of users. Military and industrial users shall inform Defense Supply Center Columbus (DSCC) when a system application requires configuration control and the applicable SMD. DSCC will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DSCC-VA, telephone (614) 692-0544.

6.5 Comments. Comments on this drawing should be directed to DSCC-VA, Columbus, Ohio 43218-3990 or telephone (614) 692-0547

6.6 Approved sources of supply. Approved sources of supply are listed in MIL-HDBK-103. The vendors listed in MIL-HDBK-103 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DSCC-VA.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		77046
		REVISION LEVEL F	SHEET 11

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 05-02-09

Approved sources of supply for SMD 77046 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML-38535 during the next revision. MIL-HDBK-103 and QML-38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DSCC-VA. This information bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML-38535. DSCC maintains an online database of all current sources of supply at <http://www.dscclia.mil/Programs/SMCR/>.

Standard microcircuit drawing PIN <u>1/</u>	Vendor CAGE number	Vendor similar PIN <u>2/</u>
7704601CA	27014	CD4093BMJ/883
7704601DA	<u>3/</u>	CD4093BMW/883
7704602CA	01295	CD4093BF3A

1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the Vendor to determine its availability.

2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.

3/ No longer available from an approved source of supply.

Vendor CAGE
number

01295

Vendor name
and address

Texas Instruments Inc.
Semiconductor Group
8505 Forest Ln.
P.O. Box 660199
Dallas, TX 75243
Point of contact: U.S. Highway 75 South
P.O. Box 84, M/S 853
Sherman, TX 75090-9493

27014

National Semiconductor
2900 Semiconductor Drive
P.O. Box 58090
Santa Clara, CA 95052-8090

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.