



Products

Industries

Resources

About TE

My Account

Innovation

Support Center

Home > Products > RF & Coax > Product Feature Selector > Product Details

1-1337406-0 Product Details

Share

Print

Email



1-1337406-0

TE Internal Number: 1-1337406-0
 Active

N Series RF Connectors

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - RF
- Jack
- Coaxial Cable Termination Type = Solder/Clamp
- Applies To Cable
- Coaxial Cable Type (RG/U or Mfg.) = 213, 8A, PSF 1/4M, Raychem 5012A1422, Raychem 5012E1339, Raychem 5012E1632, Raychem EPD 29108Q, Raychem EPD 71535Q, URM 67

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- TYPE-N STRAIGHT JACK SOLDER 50 OHM PSF 1/4M, RG8A/U,... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- [Gender](#) = Jack
- Wire/Cable Type = Coaxial Cable
- [Grade](#) = Commercial
- Lightning/EMP Protection = None
- [Dielectric Material](#) = PTFE
- Weatherproof = No
- Flats Dimension = 15.8 A/F

Mechanical Attachment:

- Panel Mount Retention = Without

Electrical Characteristics:

- Frequency = DC - 11 GHz
- Connector Impedance (Ω) = 50

Termination Features:

- Coaxial Cable Termination Type = Solder/Clamp

Body Features:

- [Body Style](#) = Straight
- [Body Plating](#) = Silver
- Body Material = Brass
- Gasket Material = White Silicone Rubber

Contact Features:

- Captured Center Contact = With
- [Center Contact Plating](#) = Silver
- Center Contact Material = Brass

Configuration Features:

- Coaxial Cable Type (RG/U or Mfg.) = 213, 8A, PSF 1/4M, Raychem 5012A1422, Raychem 5012E1339, Raychem 5012E1632, Raychem EPD 29108Q, Raychem EPD 71535Q, URM 67

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Environmental:

- Operating Temperature (Max.) (°C) = 165

Conditions for Usage:

- Applies To = Cable

Packaging Features:

- Packaging Method = Individual
- Packaging Quantity = 50

Other:

- Brand = Greenpar

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

