

1473247-1 ✓ ACTIVE

MQS

TE Internal #: 1473247-1


81 Position, Black, Cover Assembly, PBT, 90 ° Cable Exit, -40 – 120 °

C [-40 – 248 °F]

[View on TE.com >](#)



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: **81**

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Cover Assembly**

Primary Product Material: **PBT**

Cable Exit Angle: **90 °**

## Features

### Product Type Features

Sealable	Yes
Protection & Strain Relief Accessory Type	Cover Assembly

### Configuration Features

Number of Positions	81
---------------------	----

### Body Features

Primary Product Color	Black
Primary Product Material	PBT
Cable Exit Angle	90 °

### Mechanical Attachment

Strain Relief	Without
---------------	---------

### Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

### Packaging Features

Packaging Method	Bag
Packaging Quantity	70

## Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Customers Also Bought



TE Part #344079-1  
RECEPT. HSG. ASSY. 8 WAY



TE Part #1-480487-2  
FASTON 187 FLAG HSG NYLON NAT LP



TE Part #964282-2  
JPT A REC 2.8 Contact SWS Sn



TE Part #CAT-N01-AT063064  
0.63 mm to 0.64 mm Automation Ready Terminals for Advanced Automotive Wire Harness Assembly Automation



TE Part #6-1355118-1  
MQS VERRIEGLUNG



TE Part #1473244-3  
MQS/JPT 81POS PLUG ASSY



TE Part #2236369-1  
61103 DVI LOCKING SEALING PLUG #16



TE Part #3-653846-2  
DRAHTCRIMPER #16

## Documents

### Product Drawings

#### MQS 81P LEVER(R) ASSY

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473247-1\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473247-1\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1473247-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English

#### Application Specification

English

### Instruction Sheets

#### UNSEALED GET/MCP 81/40 SLIDER LEVER TYPE CONNECTOR

Japanese



**Instruction Sheet (non U.S.)**

Japanese

**Instruction Sheet (non U.S.)**

English

**Instruction Sheet (non U.S.)**

Japanese