

Crimp Information Sheet

DELPHI

Terminal Part Number: 12198102
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,30 - 2,10
 Seal(s): 15327860 | 12162575 | 15324976 | 15339967 | 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50 / 15324976		1,50	75	1,20	0,05	2,05	0,10	3,50	0,10	4,00	0,10
2010 0,50 / 15339967		1,50	75	1,20	0,05	2,05	0,10	3,50	0,10	4,00	0,10
2010 0,50 / 15324974		1,50	75	1,20	0,05	2,05	0,10	3,50	0,10	4,00	0,10
2010 0,75 / 15324976		1,75	90	1,30	0,05	2,05	0,10	3,70	0,10	4,00	0,10
2010 0,75 / 15324974		1,75	90	1,30	0,05	2,05	0,10	3,70	0,10	4,00	0,10
2010 1,00 / 15327860		1,95	115	1,30	0,05	2,20	0,10	4,10	0,10	4,10	0,10
2010 1,00 / 12162575		1,95	115	1,30	0,05	2,20	0,10	4,10	0,10	4,05	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 12198102
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 10,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*



Cable Type codes: 2013
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 5,50 - 6,00
Seal(s): 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2013 10,00 / 15324974		5,75	75	1,20	0,05	2,05	0,10	3,50	0,10	4,00	0,10

Cable type code legend:

2013:

Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PUR, PVC, SYNTHRESIN, XLPE, XLPE/PVDF
Insul. Wall Designator: THIN



Terminal Part Number: 12198102

Surface Plating: SN

Material Thickness [mm]: -

Cross Section [mm²]: 0,50

Cable Type codes: 2053

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 1,40 - 1,60

Seal(s): 10756963

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2053 0,50 / 10756963		1,50	70	1,20	0,05	2,20	0,10	3,70	0,10	4,00	0,10

Cable type code legend:

2053: PSA T2 ZH ID, PSA T3 ZH ID, PSA T4 ZH ID



Industry Designator: PSA

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: POLYOLEFIN, X-POLY

Insul. Wall Designator: ID



Terminal Part Number: 12198102

Surface Plating: SN

Material Thickness [mm]: -

Cross Section [mm²]: 0,50

Cable Type codes: 3004

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 1,50 - 1,70

Seal(s): 15324974 | 15404535

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 0,50 / 15324974		1,60	75	1,20	0,05	2,05	0,10	3,70	0,10	4,00	0,10
3004 0,50 / 15404535		1,60	75	1,20	0,05	2,05	0,10	3,70	0,10	4,00	0,10

Cable type code legend:

3004: AVSS

Industry Designator: JIS/JA

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPE, X-PVC

Insul. Wall Designator: THIN

