Part Number : 480372200
Product Description : Universal Serial Bus (USB) Shielded I/O Plug, Type A, Right-Angle, Surface Mount, Straight Tab 3.80mm, 0.76µm Gold (Au) Plating, PCB Thickness 1.60mm, Tape on Reel Package, Lead-Free
Series Number : 48037
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

480372200_sd.pdf

PK-48037-210-002.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

EE-48204-001-001.pdf

EE-67329-001-001.pdf

Specifications

PS-48037-001-001.pdf

TS-48037-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	48037
Description	Universal Serial Bus (USB) Shielded I/O Plug, Type A, Right-Angle, Surface Mount, Straight Tab 3.80mm, 0.76µm Gold (Au) Plating, PCB Thickness 1.60mm, Tape on Reel Package, Lead-Free
Application	Wire-to-Board
Comments	Straight Tab 3.80mm
Component Type	Plug
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822350623230

Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Shield Type	Full Shield

Downloaded from Arrow.com.

Voltage - Maximum	150V AC (RMS)

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Mounting Style	Top-Mount
Net Weight	2.020/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1

Downloaded from Arrow.com.

Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	USB Type A Receptacle

This document was generated on Oct 06, 2026

Downloaded from Arrow.com.