

CATALOG LISTING
6AT10

PAGE 1 OF 1

ISSUE
M
14

REVISIONS

A 205419
DLT
24 APR 02

CHECK

24 APR 02

SAV

CHECK

24 APR 02

RASTER
DRAWN

REPLACES

RELEASE NO.

CHECK


CHECK

24 APR 02

SAV

CHECK

24 APR 02




NOTES

- 1 - UNIT INCLUDES 3X CATALOG LISTING 1SM1 BASIC SWITCHES
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - TERMINALS ARE PLATED FOR SOLDERING
- 4 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805
- 5 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA312-AT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

ELECTRICAL DATA

SCALE

FULL

DO NOT SCALE PRINT

CONTACT ARRANGEMENT
3X SPDT

BREAK DISTANCE
.010 MIN

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT .06 LB.

250 VAC ————— 5 AMP
30 VOLTS DC RATING
INDUCTIVE ——— SEA LEVEL ——— 3 AMP
50,000 FT ——— 2.5 AMP
RESISTIVE ——— SEA LEVEL ——— 5 AMP
50,000 FT ——— 5 AMP
MAXIMUM INRUSH ——— 24 AMP