


39614000000 - 396 Series



Series: 396

Fuse 396 Datasheet

- Features:
- Lead free
 - Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistance
 - Halogen free

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog

Read Now

Electronics
News and Information

SIGN UP NOW

Feedback

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	4	
Nominal Melting I ² T (A ² sec)	27	
Interrupting Rating	100A@125VAC	
Min Operating Temp °C	-40	
Max Operating Temp (°C)	85	
Moisture Sensitivity Level	MIL-STD-202 Method 106	
Nominal Power Dissipation (W)	400	
Nominal Voltage Drop (mV)	110	
Nominal Cold Resistance (Ohms)	0.01642	
Opening	Slo-Blo/Time Lag (T)/Time Delay	
Package Size	TE5 (8.5x8mm)	
VAC (V)	125	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

- About Littelfuse**
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse**
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources**
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents