

HC-B-G-M25-EC-AL - Cable gland



1411446

<https://www.phoenixcontact.com/us/products/1411446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



EVO EMC cable gland with bayonet locking, B series, size M25, cable diameter: 11 ... 16 mm

Commercial data

Item number	1411446
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APM
Catalog page	Page 605 (C-2-2019)
GTIN	4046356932387
Weight per piece (including packing)	81.6 g
Weight per piece (excluding packing)	80.8 g
Customs tariff number	85389099
Country of origin	DE

HC-B-G-M25-EC-AL - Cable gland

1411446

<https://www.phoenixcontact.com/us/products/1411446>



Technical data


Product properties

Product type	Cable gland with bayonet locking
Application	EMC
No. of conductors	1
Type of the screw connection	M25
Shielded	yes

Data management status

Article revision	01
------------------	----

Dimensions

Dimensional drawing	
Width	54 mm
Height	57.5 mm
Depth	57.3 mm
Wrench size, union nut	27 mm

Material specifications

Color	aluminum
Material Pressure screw	Brass, nickel-plated
Seal material O-ring	NBR
Seal material Cable seal	NBR
Housing material	Die-cast aluminum, corrosion resistant
Material for screw connection	Aluminum

Cable/line

External cable diameter Cable 1	11 mm ... 16 mm
---------------------------------	-----------------

Mechanical properties

Mechanical data

Type of the screw connection	M25
------------------------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
	4 (UL 50e)

HC-B-G-M25-EC-AL - Cable gland



1411446

<https://www.phoenixcontact.com/us/products/1411446>

Enclosure rating (NEMA)	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C (static)

HC-B-G-M25-EC-AL - Cable gland


1411446

<https://www.phoenixcontact.com/us/products/1411446>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-G-M25-EC-AL - Cable gland



1411446


<https://www.phoenixcontact.com/us/products/1411446>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411446>




cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026



EAC
Approval ID: RU C-DE.AI30.B.01102



EAC-RoHS
Approval ID: RU D-DE.HB35.B.00387

cULus Recognized

HC-B-G-M25-EC-AL - Cable gland



1411446

<https://www.phoenixcontact.com/us/products/1411446>

Classifications

ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140801

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

HC-B-G-M25-EC-AL - Cable gland



1411446
<https://www.phoenixcontact.com/us/products/1411446>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1c54e765-8a60-49a2-93c7-cefebca5b43c

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com