


 No.390, Yong He Road, Shanghai 200072, China		TECHNICAL DATA SHEET CABLE ASSEMBLY		PART NUMBER : R296.701.377 Issue : 0909A Date : 2009-02-25	
Customer : Arrow central Europe GmbH		Specification : E074435		Issue : N/A Date : 17/11/2008	
<i>All dimensions are in mm</i>					
					
Connectors designation :		Connector 1 : UMP Right Angle Plug H2.6 Snap Cable2/50S(R107.111.200)		Connector 2: UMP Right Angle Plug H2.6 Snap Cable2/50S(R107.111.200)	
Cable designation :		Flexible Cable 2/50S(C291.140.087)			
Nominal length :		Lg: 250mm			
Cable colour :		Brown			
Outer diameter :		1.8mm			
ELECTRICAL CHARACTERISTICS :					
High Frequency Characteristic impedance : 50± 2 Ohms Frequency range : 0-3GHz Insertion Loss(Max.) : 0.77dB@1G V S W R : TBT			Low Frequency Insulation Resistance : 1000 MOhms min Voltage Rating : 100 Veff max Dielectric withstanding voltage: 350 Veff min		
MECHANICAL CHARACTERISTICS :					
Recommend min. bending radius : 9mm					
Life (connectors) : 3000 cycles					
ENVIRONMENTAL CHARACTERISTICS : Operating temperature range : -40℃ to +90℃ Remark : NA Attachment :				CUSTOMER'S APPROVAL Service or Company's stamp Name Date	
Howell Wang	0909A	2009-02-25	Creation	T YU	
Name	Issue	Date	Modification	Checked by	