







HOLE LAYOUT $\oplus 0.05$




Specifications:

Contact rating:	0.3A, 50V DC
Contact resistance:	30mOhm max.
Insulation resistance:	100MOhm min. at 500V DC for 1 minute
Dielectric strength:	500V AC (50/60Hz, 2mA) for 1 minute
Operating temperature:	-10°C to +60°C
Mechanical life:	10 000 cycles
Operating force:	200 +/-100gf
Soldering conditions:	pre-heat: max. 100°C, max. 100sec. wave soldering: max. 260°C, max. 6sec.

Material:

Terminal: brass strip, silver plated
Frame: SPCC, nickel plated
Base: phenolic resin, natural
Contact plate: brass strip, silver plated
Spring: SWC, temper
Slider: PA 66, black

CIRCUIT DIAGRAM C: COMMON PIN BOTTOM VIEW



Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	MFP 12504	
			10/16	dr		
					30 37 00	
Modifications	Date	Name	knitter-switch		Page 1/1	