
Part Number : 530150810
Product Description : 2.00mm Pitch MicroBlade Wire-to-Board Header, Right-Angle, 8 Circuits
Series Number : 53015
Status : Obsolete
Product Category : PCB Headers and Receptacles



Documents and Resources

Specifications

530159200-SPK-200.pdf

PS-51004-002-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	53015
Description	2.00mm Pitch MicroBlade Wire-to-Board Header, Right-Angle, 8 Circuits
Application	Wire-to-Board
Comments	Replacement part is not a drop in replacement. All of related parts, crimp terminal/50011, housing/51004 and header/53014 & 53015 need to be replaced to Micro-Latch series (50212 / terminal, 51065/housing, 53253/ ST hdr and 53254/RA hdr).
Component Type	PCB Header
Product Name	MicroBlade
UPC	800753566453

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Durability (mating cycles max)	30
First Mate / Last Break	No

Obsolete

Downloaded from Arrow.com.

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
Packaging Type	Bag
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.50mm
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Through Hole

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch MicroBlade Wire-to-Wire Crimp Terminals	50011
MicroBlade Single Row Receptacle Housings	51004

Downloaded from Arrow.com.