


**MODEL:** MJ-2506N | **DESCRIPTION:** AUDIO JACK**FEATURES**

- through hole design
- internal tip switch

**SPECIFICATIONS**


| parameter                  | conditions/description | min | typ   | max | units  |
|----------------------------|------------------------|-----|-------|-----|--------|
| rated input voltage        |                        |     | 12    |     | Vdc    |
| rated input current        |                        |     |       | 1   | A      |
| contact resistance         |                        |     |       | 30  | mΩ     |
| insulation resistance      | at 500 Vdc             | 100 |       |     | MΩ     |
| voltage withstand          | for 1 minute           |     |       | 500 | Vac    |
| insertion/withdrawal force |                        | 0.3 |       | 3   | kg     |
| operating temperature      |                        | -25 |       | 85  | °C     |
| life                       |                        |     | 5,000 |     | cycles |
| flammability rating        | UL94V-0                |     |       |     |        |
| RoHS                       | yes                    |     |       |     |        |

**SOLDERABILITY**



| parameter      | conditions/description                 | min | typ | max | units |
|----------------|----------------------------------------|-----|-----|-----|-------|
| wave soldering | dipped in solder pot for 5±0.5 seconds | 255 | 260 | 265 | °C    |

MECHANICAL DRAWING


units: mm  
tolerance:  
X, ±0.50 mm  
X.X ±0.30 mm  
X.XX ±0.20 mm  
PCB: ±0.05 mm  
unless otherwise specified



| DESCRIPTION | MATERIAL                  | PLATING/COLOR |
|-------------|---------------------------|---------------|
| terminal 1  | brass t=0.35 mm           | silver        |
| terminal 2  | phosphor copper t=0.25 mm | silver        |
| terminal 3  | brass t=0.35 mm           | silver        |
| bushing     | copper alloy              | nickel        |
| housing     | PBT (UL94V-0)             | black         |



Recommended PCB Layout  
Top View



|           |            |
|-----------|------------|
| Model No. | MJ-2506N   |
| Schematic |            |
| PIN       |            |
| 1         | sleeve     |
| 2         | tip        |
| 3         | tip switch |

REVISION HISTORY

| rev. | description                                                                                   | date       |
|------|-----------------------------------------------------------------------------------------------|------------|
| 1.0  | initial release                                                                               | 11/01/2005 |
| 1.01 | updated datasheet                                                                             | 09/12/2018 |
| 1.02 | brand update                                                                                  | 10/04/2019 |
| 1.03 | product reengineered for improved manufacturability and production yield, see PCN for details | 07/26/2023 |
| 1.04 | CUI Devices rebranded to Same Sky                                                             | 09/12/2024 |
| 1.05 | changed terminal plating to be silver                                                         | 03/10/2025 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**