

Catalog No. TYZ525M

Description: CBL TIE 50LB 7IN AQUAMARINE ETFE

UPC No 786210770444

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 185mm (7.3 Inches), Width of 4.1mm (0.2 Inch), Thickness of 1.6mm (0.06 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds), 100 Pack

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Fluoropolymer ETFE
Color	Aqua
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.2 in , 4.1 mm
Length	7.3 in , 185 mm
Thickness	0.06 in , 1.6 mm
Bundle Diameter	0.25 to 1.75 in , 6.4 to 44.5 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.1 mm
Length belt/tape/tie	185 mm
Length belt/tape/tie	7.3 inch
Tie thickness	1.6 mm

by ABB

ETIM	EC000046 Cable tie
Tie thickness	0.06 inch
Max. bundle diameter	44.5 mm
Min. holding force	222 N
Operation temperature	-45-+150 °C
Operation temperature	-49-+302 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Other
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	N
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0