By using this site, you agree with our use of cookies. Read our Cookie Policy

Want to know more? I consent to cookies

382W042-25/86-0

382W042-25/86-0



Raychem

TE Internal #: **320777-000**
TE Internal Description: **382W042-25/86-0**
Alias #: **7-1192431-6**

Molded Part Shape : **Y Shape**
Number of Branches/Legs : **3**
Material Code : **25**
Material Systems Code : **25**
Adhesive Pre-Coat : **Yes**

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Feedback

Documents | Features | Product Compliance

Product Drawings

382W042-25/86-0

382W042-25/86-0 English

Datasheets & Catalog Pages

1654025_Sec4_-25

ENG_CS_1654025_Sec4_-25_0313.pdf English

Product Environmental Compliance

Safety Datasheet

DUT_MSDS_RAY3143-EC-DUT_2014-06-11_3143ECN.pdf Dutch

ENG_MSDS_RAY3143-EC-ENG_2014-06-11_3143ECE.pdf English

Safety Datasheet

FRE_MSDS_RAY3143-EC-FRE_2014-06-11_3143ECF.pdf French

Safety Datasheet

GER_MSDS_RAY3143-EC-GER_2014-06-11_3143ECD.pdf German

Safety Datasheet

ITA_MSDS_RAY3143-EC-ITA_2014-06-11_3143ECI.pdf Italian

Safety Datasheet

SPA_MSDS_RAY3143-EC-SPA_2014-06-11_3143ECS.pdf Spanish

Safety Datasheet

SWE_MSDS_RAY3143-EC-SWE_2014-06-11_3143ECW.pdf Swedish

Downloaded from Arrow.com.

ENG_MSDS_RAY3143-US-ENG_B.pdf English

Safety Datasheet

FRE_MSDS_SDS0190-EC-FRE_2014-04-10.pdf French

Safety Datasheet

ITA_MSDS_SDS0190-EC-ITA_2014-04-10.pdf Italian

Safety Datasheet

NOR_MSDS_SDS0190-EC-NOR_2014-04-10.pdf Norwegian

Safety Datasheet

DAN_MSDS_SDS0190-EC-DAN_2014-04-10.pdf Danish

Safety Datasheet

ENG_MSDS_SDS0190-EC-ENG_2014-04-10.pdf English

Safety Datasheet

GER_MSDS_SDS0190-EC-GER_2014-04-10.pdf German

Safety Datasheet

SPA_MSDS_SDS0190-EC-SPA_2014-04-10.pdf Spanish

Safety Datasheet

SWE_MSDS_SDS0190-EC-SWE_2014-02-21_SDS190ECW.pdf Swedish

Safety Datasheet

DUT_MSDS_SDS0190-EC-DUT_2014-04-10.pdf Dutch

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Shape : **Y Shape**
Size Code : **042**

Configuration Features

Number of Branches/Legs : **3**

Body Features

Material Code : **25**
Material Systems Code : **25**
Adhesive Pre-Coat : **Yes**
Material : **Fluid Resistant Modified Elastomer**

Dimensions

Inside Diameter Range (Leg 1) : **4 – 9 mm [.16 – .35 in]**
Inside Diameter Range (Body) : **8 – 20 mm [.31 – .79 in]**
Inside Diameter Range (Leg 2) : **4 – 9 mm [.16 – .35 in]**

Usage Conditions

Operating Temperature Range : **-75 – 150 °C [-103 – 302 °F]**

Operation/Application

Power Cable Accessory : **No**

Downloaded from Arrow.com.

Industry Standards	Government Qualified : **No**

Other	Molded Part Shape Code : **382W** Fluid/Chemical Resistance : **Long-Term Exposure at High Temperature** Adhesive Options : **/86 Precoat** Adhesive Type : **High Performance Pre-Coat Adhesive** Adhesive Code : **86**

Downloaded from Arrow.com.