




PRODUCT NO.  
SEE TABLE



|             |          |     |          |                                       |                      |            |                |
|-------------|----------|-----|----------|---------------------------------------|----------------------|------------|----------------|
| mat'l. code |          |     |          | surface                               | tolerance            | projection | product family |
| —           |          |     |          | ISO 1302                              | ISO 406<br>ISO 1101  | ISO 1101   | CARD CONN      |
| lir         | ecn no   | dr  | date     | tolerances unless otherwise specified |                      | INCH/MM    | title          |
| J           | V61635   | MDF | 11/21/96 | angles                                | linear               |            |                |
| K           | V70999   | LSS | 12/11/97 |                                       |                      |            |                |
| L           | V02386   | AZ  | 10/05/00 | 0° ± 2°                               | xxxx $\pm .0020/.05$ | scale 4:1  |                |
| M           | M05-0181 | MHT | 8/22/05  | dr                                    | L. SANDERS           | 12/11/97   |                |
| N           | M06-0117 | AEA | 6/26/06  | eng                                   | H. SUNDY             | 12/11/97   |                |
| P           | M07-0137 | MHT | 2/26/07  | chr                                   | H. SUNDY             | 12/11/97   |                |
| R           | M09-0093 | MHT | 6/22/09  | app                                   | H. SUNDY             | 12/11/97   |                |
| sheet       | revision | R   | R        | R                                     | R                    | R          |                |
| index       | sheet    | 1   | 2        | 3                                     | 4                    | 5          | 6              |




dwg no 67477  
sheet 1 of 6  
size A3  
type Product Customer Drawing



Copyright FCI

form A3



1. HOUSING MATERIAL.  
FILLED HIGH TEMPERATURE NYLON  
NOTES. PER UL 94V-0  
COLOR. BLACK
2. TERMINAL MATERIAL.  
BODY. BRASS. .010/.25 THICK.  
SPRING. BE-CU. HEAT TREATED  
BODY PLATING.  
40 MICROINCH / 1.02 MICRON GOLD  
OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.  
SOLDER TAIL. 100u"/2.54u" PURE TIN (NOTE 8) OVER 50u"/1.27 Ni.  
SPRING PLATING. GOLD FLASH
3. APPLICATION INFORMATION.  
A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN IN FIG. 1.  
B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA.  
C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±.51.
- ④ TERMINAL MATERIAL:  
BODY. BRASS. .010/.25 THICK.  
SPRING. BE-CU. HEAT TREATED  
BODY PLATING.  
40 MICROINCH / 1.02 MICRON GOLD  
OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.  
SOLDER TAIL: GOLD FLASH OVER 50u"/1.27u Ni.1.27 Ni.  
SPRING PLATING. GOLD FLASH
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑥ THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ⑧ THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WISKER GROWTH IN ALL INTERCONNECT REQUIREMENTS

|             |          |                                       |           |            |                          |
|-------------|----------|---------------------------------------|-----------|------------|--------------------------|
| mat'l. code |          | surface                               | tolerance | projection | product family           |
| -           |          | ISO 1302                              | ISO 406   |            | CARD CONN                |
| ISO 1101    |          | tolerances unless otherwise specified | ISO 1101  |            |                          |
| ltr         | ecr no   | dr                                    | date      |            | title                    |
| R           |          |                                       |           |            | GUIDE PIN                |
|             |          |                                       |           |            | CARD CONNECTOR           |
|             |          |                                       |           |            | dwg no                   |
|             |          |                                       |           |            | 67477                    |
|             |          |                                       |           |            | sheet 2 of 6             |
|             |          |                                       |           |            | size                     |
|             |          |                                       |           |            | A3                       |
|             |          |                                       |           |            | type                     |
|             |          |                                       |           |            | Product Customer Drawing |
| sheet       | revision |                                       |           |            |                          |
| index       | sheet    |                                       |           |            |                          |

Copyright FCJ  
FCJconnect.com

FCI  
FConnectron

Copyright FCI

|             |             |           |              |                 |                  |            |  |   |  |   |  |
|-------------|-------------|-----------|--------------|-----------------|------------------|------------|--|---|--|---|--|
| 1           |             | 2         |              | 3               |                  | 4          |  | 5 |  | 6 |  |
| PRODUCT NO. | NO. OF POS. | DIM. A    | DIM. B       | INSULATION PLUG | LEAD FREE OPTION |            |  |   |  |   |  |
| 67477-001   | 2X1         | .00/.0    | .358/9.09    | NO              | NOTE 6,7         | UNASSIGNED |  |   |  |   |  |
| -002        | 2X2         | .10/2.5   | .458/11.63   | NO              |                  | OBSOLETE   |  |   |  |   |  |
| -003        | 2X3         | .20/5.0   | .558/14.17   | NO              |                  | OBSOLETE   |  |   |  |   |  |
| -004        | 2X4         | .30/7.6   | .658/16.71   | NO              |                  | OBSOLETE   |  |   |  |   |  |
| -005        | 2X5         | .40/10.1  | .758/19.25   |                 |                  |            |  |   |  |   |  |
| -006        | 2X6         | .50/12.7  | .858/21.79   |                 |                  |            |  |   |  |   |  |
| -007        | 2X7         | .60/15.2  | .958/24.33   |                 |                  |            |  |   |  |   |  |
| -008        | 2X8         | .70/17.7  | 1.058/26.87  |                 |                  |            |  |   |  |   |  |
| -009        | 2X9         | .80/20.3  | 1.158/29.41  |                 |                  |            |  |   |  |   |  |
| -010        | 2X10        | .90/22.8  | 1.258/31.95  |                 |                  |            |  |   |  |   |  |
| -011        | 2X11        | 1.00/25.4 | 1.358/34.49  |                 |                  |            |  |   |  |   |  |
| -012        | 2X12        | 1.10/27.9 | 1.458/37.03  |                 |                  |            |  |   |  |   |  |
| -013        | 2X13        | 1.20/30.4 | 1.558/39.57  |                 |                  |            |  |   |  |   |  |
| -014        | 2X14        | 1.30/33.0 | 1.658/42.11  |                 |                  |            |  |   |  |   |  |
| -015        | 2X15        | 1.40/35.5 | 1.758/44.65  |                 |                  |            |  |   |  |   |  |
| -016        | 2X16        | 1.50/38.1 | 1.858/47.19  |                 |                  |            |  |   |  |   |  |
| -017        | 2X17        | 1.60/40.6 | 1.958/49.73  |                 |                  |            |  |   |  |   |  |
| -018        | 2X18        | 1.70/43.1 | 2.058/52.27  |                 |                  |            |  |   |  |   |  |
| -019        | 2X19        | 1.80/45.7 | 2.158/54.81  |                 |                  |            |  |   |  |   |  |
| -020        | 2X20        | 1.90/48.2 | 2.258/57.35  |                 |                  |            |  |   |  |   |  |
| -021        | 2X21        | 2.00/50.8 | 2.358/59.89  |                 |                  |            |  |   |  |   |  |
| -022        | 2X22        | 2.10/53.3 | 2.458/62.43  |                 |                  |            |  |   |  |   |  |
| -023        | 2X23        | 2.20/55.8 | 2.558/64.97  |                 |                  |            |  |   |  |   |  |
| -024        | 2X24        | 2.30/58.4 | 2.658/67.51  |                 |                  |            |  |   |  |   |  |
| -025        | 2X25        | 2.40/60.9 | 2.758/70.05  |                 |                  |            |  |   |  |   |  |
| -026        | 2X26        | 2.50/63.5 | 2.858/72.59  |                 |                  |            |  |   |  |   |  |
| -027        | 2X27        | 2.60/66.0 | 2.958/75.13  |                 |                  |            |  |   |  |   |  |
| -028        | 2X28        | 2.70/68.5 | 3.058/77.67  |                 |                  |            |  |   |  |   |  |
| -029        | 2X29        | 2.80/71.1 | 3.158/80.21  |                 |                  |            |  |   |  |   |  |
| -030        | 2X30        | 2.90/73.6 | 3.258/82.75  |                 |                  |            |  |   |  |   |  |
| -031        | 2X31        | 3.00/76.2 | 3.358/85.29  |                 |                  |            |  |   |  |   |  |
| -032        | 2X32        | 3.10/78.7 | 3.458/87.83  |                 |                  |            |  |   |  |   |  |
| -033        | 2X33        | 3.20/81.2 | 3.558/90.37  |                 |                  |            |  |   |  |   |  |
| -034        | 2X34        | 3.30/83.8 | 3.658/92.91  |                 |                  |            |  |   |  |   |  |
| -035        | 2X35        | 3.40/86.3 | 3.758/95.45  |                 |                  |            |  |   |  |   |  |
| -036        | 2X36        | 3.50/88.9 | 3.858/97.99  |                 |                  |            |  |   |  |   |  |
| -037        | 2X37        | 3.60/91.4 | 3.958/100.53 |                 |                  |            |  |   |  |   |  |
| -038        | 2X38        | 3.70/93.9 | 4.058/103.07 |                 |                  |            |  |   |  |   |  |
| -039        | 2X39        | 3.80/96.5 | 4.158/105.61 |                 |                  |            |  |   |  |   |  |
| 67477-040   | 2X40        | 3.90/99.0 | 4.258/108.15 | NO              | NOTE 6,7         |            |  |   |  |   |  |

mat'l. code

ISO 1302

surface

tolerance

ISO 406

ISO 1101

projection

product family

CARD CONN

title

GUIDE PIN

CARD CONNECTOR

dwg no

67477

sheet 3 of 6

size

A3

type

Product Customer Drawing

revision

sheet

index

form: A3

| PRODUCT NO. | NO. OF POS. | DIM. A     | DIM. B       | INSULATION PLUG | LEAD FREE OPTION |
|-------------|-------------|------------|--------------|-----------------|------------------|
| 67477-041   | 2X41        | 4.00/101.6 | 4.358/110.69 | NO              | NOTE 6,7         |
| -042        | 2X42        | 4.10/104.1 | 4.458/113.23 |                 |                  |
| -043        | 2X43        | 4.20/106.6 | 4.558/115.77 |                 |                  |
| -044        | 2X44        | 4.30/109.2 | 4.658/118.31 |                 |                  |
| -045        | 2X45        | 4.40/111.7 | 4.758/120.85 |                 |                  |
| -046        | 2X46        | 4.50/114.3 | 4.858/123.39 |                 |                  |
| -047        | 2X47        | 4.60/116.8 | 4.958/125.93 |                 |                  |
| -048        | 2X48        | 4.70/119.3 | 5.058/128.47 |                 |                  |
| -049        | 2X49        | 4.80/121.9 | 5.158/131.01 |                 |                  |
| -050        | 2X50        | 4.90/124.4 | 5.258/133.55 |                 |                  |
| -051        | 2X51        | 5.00/127.0 | 5.358/136.09 |                 |                  |
| -052        | 2X52        | 5.10/129.5 | 5.458/138.63 |                 |                  |
| -053        | 2X53        | 5.20/132.0 | 5.558/141.17 |                 |                  |
| -054        | 2X54        | 5.30/134.6 | 5.658/143.71 |                 |                  |
| -055        | 2X55        | 5.40/137.1 | 5.758/146.25 |                 |                  |
| -056        | 2X56        | 5.50/139.7 | 5.858/148.79 |                 |                  |
| -057        | 2X57        | 5.60/142.2 | 5.958/151.33 |                 |                  |
| -058        | 2X58        | 5.70/144.7 | 6.058/153.87 |                 |                  |
| -059        | 2X59        | 5.80/147.3 | 6.158/156.41 |                 |                  |
| -060        | 2X60        | 5.90/149.8 | 6.258/158.95 |                 |                  |
| -061        | 2X61        | 6.00/152.4 | 6.358/161.49 |                 |                  |
| -062        | 2X62        | 6.10/154.9 | 6.458/164.03 |                 |                  |
| -063        | 2X63        | 6.20/157.4 | 6.558/166.57 |                 |                  |
| -064        | 2X64        | 6.30/160.0 | 6.658/169.11 |                 |                  |
| 67477-065   | 2X65        | 6.40/162.5 | 6.758/171.65 | NO              |                  |
| -066 THRU   |             |            |              |                 | NOTE 6,7         |
| -100        |             |            |              |                 |                  |

OBSELETE

|             |          |    |      |                                       |            |                                  |  |            |  |                             |  |
|-------------|----------|----|------|---------------------------------------|------------|----------------------------------|--|------------|--|-----------------------------|--|
| mat'l. code |          |    |      | surface<br>ISO 1302                   |            | tolerance<br>ISO 406<br>ISO 1101 |  | projection |  | product family<br>CARD CONN |  |
| ltr         | ecn no   | dr | date | tolerances unless otherwise specified |            |                                  |  | INCH/MM    |  | title                       |  |
| R           |          |    |      | angles                                | linear     | .XX±.01/.3                       |  |            |  | GUIDE PIN                   |  |
|             |          |    |      |                                       |            | .xxx ±.005/.13                   |  |            |  | CARD CONNECTOR              |  |
|             |          |    |      | 0'±2'                                 |            | .xxx ±.0020/.05                  |  | scale 4:1  |  | dwg no                      |  |
|             |          |    |      | dr                                    | L. SANDERS | 12/11/97                         |  |            |  | sheet 4 of 6                |  |
|             |          |    |      | engr                                  | H. SUNDY   | 12/11/97                         |  |            |  | size                        |  |
|             |          |    |      | chr                                   | H. SUNDY   | 12/11/97                         |  |            |  | A3                          |  |
|             |          |    |      | appd                                  | H. SUNDY   | 12/11/97                         |  |            |  | type                        |  |
| sheet       | revision |    |      |                                       |            |                                  |  |            |  | Product Customer Drawing    |  |
| index       | sheet    |    |      |                                       |            |                                  |  |            |  |                             |  |



FCIconnect.com

Copyright FCI

| PRODUCT NO. | NO. OF POS. | DIM. A    | DIM. B       | INSULATION PLUG | LEAD FREE OPTION |
|-------------|-------------|-----------|--------------|-----------------|------------------|
| 67477-501   | 2X1         | .00/.0    | .358/9.09    | YES             | NOTE 6,7         |
| -502        | 2X2         | .10/2.5   | .458/11.63   | YES             |                  |
| -503        | 2X3         | .20/5.0   | .558/14.17   | YES             |                  |
| -504        | 2X4         | .30/7.6   | .658/16.71   | YES             |                  |
| -505        | 2X5         | .40/10.1  | .758/19.25   |                 |                  |
| -506        | 2X6         | .50/12.7  | .858/21.79   |                 |                  |
| -507        | 2X7         | .60/15.2  | .958/24.33   |                 |                  |
| -508        | 2X8         | .70/17.7  | 1.058/26.87  |                 |                  |
| -509        | 2X9         | .80/20.3  | 1.158/29.41  |                 |                  |
| -510        | 2X10        | .90/22.8  | 1.258/31.95  |                 |                  |
| -511        | 2X11        | 1.00/25.4 | 1.358/34.49  |                 |                  |
| -512        | 2X12        | 1.10/27.9 | 1.458/37.03  |                 |                  |
| -513        | 2X13        | 1.20/30.4 | 1.558/39.57  |                 |                  |
| -514        | 2X14        | 1.30/33.0 | 1.658/42.11  |                 |                  |
| -515        | 2X15        | 1.40/35.5 | 1.758/44.65  |                 |                  |
| -516        | 2X16        | 1.50/38.1 | 1.858/47.19  |                 |                  |
| -517        | 2X17        | 1.60/40.6 | 1.958/49.73  |                 |                  |
| -518        | 2X18        | 1.70/43.1 | 2.058/52.27  |                 |                  |
| -519        | 2X19        | 1.80/45.7 | 2.158/54.81  |                 |                  |
| -520        | 2X20        | 1.90/48.2 | 2.258/57.35  |                 |                  |
| -521        | 2X21        | 2.00/50.8 | 2.358/59.89  |                 |                  |
| -522        | 2X22        | 2.10/53.3 | 2.458/62.43  |                 |                  |
| -523        | 2X23        | 2.20/55.8 | 2.558/64.97  |                 |                  |
| -524        | 2X24        | 2.30/58.4 | 2.658/67.51  |                 |                  |
| -525        | 2X25        | 2.40/60.9 | 2.758/70.05  |                 |                  |
| -526        | 2X26        | 2.50/63.5 | 2.858/72.59  |                 |                  |
| -527        | 2X27        | 2.60/66.0 | 2.958/75.13  |                 |                  |
| -528        | 2X28        | 2.70/68.5 | 3.058/77.67  |                 |                  |
| -529        | 2X29        | 2.80/71.1 | 3.158/80.21  |                 |                  |
| -530        | 2X30        | 2.90/73.6 | 3.258/82.75  |                 |                  |
| -531        | 2X31        | 3.00/76.2 | 3.358/85.29  |                 |                  |
| -532        | 2X32        | 3.10/78.7 | 3.458/87.83  |                 |                  |
| -533        | 2X33        | 3.20/81.2 | 3.558/90.37  |                 |                  |
| -534        | 2X34        | 3.30/83.8 | 3.658/92.91  |                 |                  |
| -535        | 2X35        | 3.40/86.3 | 3.758/95.45  |                 |                  |
| -536        | 2X36        | 3.50/88.9 | 3.858/97.99  |                 |                  |
| -537        | 2X37        | 3.60/91.4 | 3.958/100.53 |                 |                  |
| -538        | 2X38        | 3.70/93.9 | 4.058/103.07 |                 |                  |
| -539        | 2X39        | 3.80/96.5 | 4.158/105.61 |                 |                  |
| 67477-540   | 2X40        | 3.90/99.0 | 4.258/108.15 | YES             | NOTE 6,7         |

UNASSIGNED  
OBSOLETE  
OBSOLETE  
OBSOLETE

|             |          |                     |      |                                       |            |            |      |                             |                          |
|-------------|----------|---------------------|------|---------------------------------------|------------|------------|------|-----------------------------|--------------------------|
| mat'l. code |          | surface<br>ISO 1902 |      | tolerance<br>ISO 406<br>ISO 1901      |            | projection |      | product family<br>CARD CONN |                          |
| ltr         | ec'n no  | dr                  | date | tolerances unless otherwise specified |            |            |      | title                       |                          |
| R           |          |                     |      | angles                                | linear     | INCH/MM    |      | GUIDE PIN<br>CARD CONNECTOR |                          |
|             |          |                     |      | 0'±2'                                 |            | scale 4:1  |      | dwg no                      |                          |
|             |          |                     |      | dr                                    | L. SANDERS | 12/11/97   |      |                             | sheet 5 of 6             |
|             |          |                     |      | engr                                  | H. SUNDY   | 12/11/97   |      |                             | size                     |
|             |          |                     |      | chr                                   | H. SUNDY   | 12/11/97   |      |                             | A3                       |
|             |          |                     |      | appd                                  | H. SUNDY   | 12/11/97   | type |                             | Product Customer Drawing |
| sheet       | revision |                     |      |                                       |            |            |      |                             |                          |
| index       | sheet    |                     |      |                                       |            |            |      |                             |                          |

form A3

| PRODUCT NO. | NO. OF POS. | DIM. A     | DIM. B       | INSULATION PLUG | LEAD FREE OPTION |
|-------------|-------------|------------|--------------|-----------------|------------------|
| 67477-541   | 2X41        | 4.00/101.6 | 4.358/110.69 | YES             | NOTE 6,7         |
| -542        | 2X42        | 4.10/104.1 | 4.458/113.23 |                 |                  |
| -543        | 2X43        | 4.20/106.6 | 4.558/115.77 |                 |                  |
| -544        | 2X44        | 4.30/109.2 | 4.658/118.31 |                 |                  |
| -545        | 2X45        | 4.40/111.7 | 4.758/120.85 |                 |                  |
| -546        | 2X46        | 4.50/114.3 | 4.858/123.39 |                 |                  |
| -547        | 2X47        | 4.60/116.8 | 4.958/125.93 |                 |                  |
| -548        | 2X48        | 4.70/119.3 | 5.058/128.47 |                 |                  |
| -549        | 2X49        | 4.80/121.9 | 5.158/131.01 |                 |                  |
| -550        | 2X50        | 4.90/124.4 | 5.258/133.55 |                 |                  |
| -551        | 2X51        | 5.00/127.0 | 5.358/136.09 |                 |                  |
| -552        | 2X52        | 5.10/129.5 | 5.458/138.63 |                 |                  |
| -553        | 2X53        | 5.20/132.0 | 5.558/141.17 |                 |                  |
| -554        | 2X54        | 5.30/134.6 | 5.658/143.71 |                 |                  |
| -555        | 2X55        | 5.40/137.1 | 5.758/146.25 |                 |                  |
| -556        | 2X56        | 5.50/139.7 | 5.858/148.79 |                 |                  |
| -557        | 2X57        | 5.60/142.2 | 5.958/151.33 |                 |                  |
| -558        | 2X58        | 5.70/144.7 | 6.058/153.87 |                 |                  |
| -559        | 2X59        | 5.80/147.3 | 6.158/156.41 |                 |                  |
| -560        | 2X60        | 5.90/149.8 | 6.258/158.95 |                 |                  |
| -561        | 2X61        | 6.00/152.4 | 6.358/161.49 |                 |                  |
| -562        | 2X62        | 6.10/154.9 | 6.458/164.03 |                 |                  |
| -563        | 2X63        | 6.20/157.4 | 6.558/166.57 |                 |                  |
| -564        | 2X64        | 6.30/160.0 | 6.658/169.11 |                 |                  |
| 67477-565   | 2X65        | 6.40/162.5 | 6.758/171.65 | YES             |                  |
| -566 THRU   |             |            |              |                 | NOTE 6,7         |
| -600        |             |            |              |                 |                  |

OBSOLETE



FCI  
FCIconnect.com

Copyright FCI

|             |          |                     |      |                                       |            |                |  |                             |              |
|-------------|----------|---------------------|------|---------------------------------------|------------|----------------|--|-----------------------------|--------------|
| mat'l. code |          | surface<br>ISO 1502 |      | tolerance<br>ISO 406<br>ISO 1101      |            | projection<br> |  | product family<br>CARD CONN |              |
| ltr         | ecr no   | dr                  | date | tolerances unless otherwise specified |            |                |  | title                       |              |
| R           |          |                     |      | angles                                | linear     | INCH/MM        |  | GUIDE PIN<br>CARD CONNECTOR |              |
|             |          |                     |      | 0'±2"                                 |            | scale 4:1      |  | dwg no                      |              |
|             |          |                     |      | dr                                    | L. SANDERS | 12/11/97       |  |                             | sheet 6 of 6 |
|             |          |                     |      | eng                                   | H. SUNDY   | 12/11/97       |  |                             | size         |
|             |          |                     |      | chr                                   | H. SUNDY   | 12/11/97       |  |                             | A3           |
|             |          |                     |      | appd                                  | H. SUNDY   | 12/11/97       |  |                             |              |
| sheet       | revision |                     |      |                                       |            |                |  |                             |              |
| index       | sheet    |                     |      |                                       |            |                |  |                             |              |

form: A3