


Bulk Metal® Foil Ultra High Technology Precision Trimming Potentiometers, 3/8" Square, RJ24 Style, Designed to Meet or Exceed the Requirements of MIL-PRF-39035, Char. H with a Smooth and Unidirectional Output



INTRODUCTION

Vishay Foil Resistors (VFR) precision trimmers have the Bulk Metal® Foil resistive element which possesses a unique inherent temperature and load life stability. Plus, their advanced virtually back lash-free adjustment mechanism makes them easy to set quickly and accurately and keeps the setting exactly on target.

FEATURES

- Temperature coefficient of resistance (TCR): ± 10 ppm/°C (-55 °C to +150 °C ref. at +25 °C); through the wiper ⁽²⁾; ± 25 ppm/°C (see table 2 for low values)
- A smooth and unidirectional resistance with RoHS* leadscrew adjustment COMPLIANT
- Load life stability: 0.1 % typical ΔR , 1.0 % maximum ΔR under full rated power at +85 °C for 10 000 h
- Settability: 0.05 % typical; 0.1 % maximum
- Setting stability: 0.1 % typical; 0.5 % maximum
- Power rating: 0.25 W at +85 °C
- Resistance range: 5 Ω to 10 k Ω
- Resistance tolerance: ± 5 %, ± 10 %
- "O"-ring prevents ingress of fluids during any board cleaning operation
- Electrostatic discharge (ESD) up to 25 000 V
- Terminal finish: tin/lead or lead free






TABLE 1 - MODEL SELECTION

MODEL	TERMINATION STYLE	AVERAGE WEIGHT (g)	POWER RATING at +85 °C AMBIENT	NO. OF TURNS
1260	W-edge mount, top adjust	0.4	0.25 W	21 $\pm$ 2
	X-edge mount, side adjust			

Note

- See figure 1

TABLE 2 - 1260 (RJ24 STYLE) SERIES ELECTRICAL SPECIFICATIONS

Temperature Coefficient of Resistance (TCR) 50 Ω to 10 k Ω End-to-end ⁽¹⁾	± 10 ppm/°C maximum (-55 °C to +150 °C, +25 °C ref.)
Temperature Coefficient of Resistance (TCR) 5 Ω , 10 Ω and 20 Ω Through the wiper ⁽²⁾	± 20 ppm/°C ± 25 ppm/°C
Stability Load life at 10 000 h	0.1 % typical ΔR 1.0 % maximum ΔR (under full rated power of 0.25 W at +85 °C)
Power Rating ⁽³⁾	0.25 W at +85 °C
Settability	0.05 % typical; 0.1 % maximum
Setting Stability	0.1 % typical; 0.5 % maximum
Contact Resistance Variation - CRV (noise)	3 Ω typical; 10 Ω maximum
Hop-off	0.25 % typical; 1.0 % maximum
High-Frequency Operation Rise/decay time Inductance Capacitance	1 ns without ringing 0.08 μ H typical 0.5 pF typical
Operating Temperature Range	-55 °C to +150 °C

TABLE 3 - VALUES VS. TOLERANCES



STANDARD RESISTANCE VALUES (in Ω)	STANDARD TOLERANCE
5, 10	± 10 %
20, 50, 100, 200, 500, 1K, 2K, 5K, 10K	± 5 %

TABLE 4 - MECHANICAL SPECIFICATIONS

Adjustment Turns	21 $\pm$ 2
Mechanical Stops	Wiper idles - no discontinuity
Internal Terminations	All welded - no flux
Case Material	Diallyl-phthalate: black (DAP)
Shaft Torque	3 oz. in. maximum
Backlash	0.005 % typical

FIGURE 1 - SCHEMATIC AND DIMENSIONS in Inches (Millimeters)



1260W



STANDARD MARKING:

Model No.
Date Code
Resistance Value
Tolerance
Termination Finish - in case of
Lead Free (L.F)

1260X



NOTES:

Adjustment screw 0.090" (2.29 mm) diameter with 0.020" (0.51 mm) x 0.031" (0.79 mm) slot. Model 1260 has solder plated copper terminal pins. 0.024" (0.61 mm) diameter, 0.300" (7.62 mm) length minimum.

FIGURE 2 - POWER DERATING CURVE




TABLE 5 - COMPARISON

	MIL-PRF-39035/2 CHARACTERISTIC H ⁽⁴⁾	1260 MAXIMUM
TEST GROUP I Conditioning Contact resistance variation - CRV (noise) Immersion	$\pm 1.0 \%$ $\pm 3.0 \%$ or 3Ω ⁽⁵⁾ No continuous stream of bubbles	$\pm 0.5 \%$ 3 Ω typical, 10 Ω maximum No continuous stream of bubbles
TEST GROUP Ia Visual and mechanical Actual effective electrical travel End resistance Dielectric withstanding voltage - DWV Per MIL-STD-202, methods 301 and 105 Atmospheric pressure Barometric pressure Insulation resistance Shaft torque Thermal shock Setting stability	No failures 10 to 25 turns 2 % or 2 Ω ⁽⁵⁾ 600 V _{AC} , 1 min 250 V _{AC} , 1 min $\geq 1000 M\Omega$ 3 oz. in. maximum $\pm 1.0 \%$ $\pm 1.0 \%$	No failures 21 ± 2 turns 2 Ω for values $\leq 1 k\Omega$; 5 Ω for values $\geq 2 k\Omega$; 600 V _{AC} , 1 min 250 V _{AC} , 1 min $> 1000 M\Omega$ 3 oz. in. maximum $\pm 0.5 \%$ $\pm 0.5 \%$
TEST GROUP II Solderability	Per MIL-STD-202, method 208	Per MIL-STD-202, method 208
TEST GROUP III Resistance temperature characteristic - TCR Moisture resistance Contact resistance variation - CRV (noise)	$\pm 0.005 \%/^{\circ}\text{C}$ ($\pm 50 \text{ ppm}/^{\circ}\text{C}$) $\pm 1.0 \%$ 3.0 % or 3 Ω ⁽⁵⁾	$\pm 0.001 \%/^{\circ}\text{C}$ ($\pm 10 \text{ ppm}/^{\circ}\text{C}$) $\pm 0.5 \%$ 3 Ω typical, 10 Ω maximum
TEST GROUP IV Settability Shock Setting stability Vibration Setting stability Contact resistance variation - CRV (noise) Salt spray	$\pm 1.0 \%$ $\pm 1.0 \%$ $\pm 1.0 \%$ $\pm 1.0 \%$ $\pm 1.0 \%$ 3.0 % or 3 Ω ⁽⁵⁾ No corrosion	$\pm 0.1 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ 3 Ω typical, 10 Ω maximum No corrosion
TEST GROUP V Solder heat Low-temperature operation Setting stability Low-temperature storage High-temperature exposure Setting stability Contact resistance variation - CRV (noise) Integrity of shaft	$\pm 1.0 \%$ $\pm 1.0 \%$ $\pm 2.0 \%$ $\pm 1.0 \%$ $\pm 3.0 \%$ $\pm 2.0 \%$ 3.0 % or 3 Ω ⁽⁵⁾ No loosening or breakage	$\pm 0.1 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ $\pm 0.5 \%$ 3 Ω typical, 10 Ω maximum No loosening or breakage
TEST GROUP VI Rotational life (200 cycles) Contact resistance variation - CRV (noise) Terminal strength	$\pm 2.0 \%$ 3.0 % or 3 Ω ⁽⁵⁾ 2 lbs.	$\pm 2.0 \%$ 3 Ω typical, 10 Ω maximum 2 lbs.
TEST GROUP VII Life (2000 h) at + 85 °C Life (10 000 h) at + 85 °C	$\pm 3.0 \%$ $\pm 5.0 \%$	$\pm 0.1 \%$ typical, $\pm 1.0 \%$ maximum $\pm 0.1 \%$ typical, $\pm 1.0 \%$ maximum
TEST GROUP VIII Solvent resistance	No failures	No failures

Notes

- (1) Maximum TCR applies to the 3 σ (sigma) limit or 99.73 % of a production lot. (Measured end-to-end with wiper off the element.)
- (2) Measurements of TCR through the wiper are influenced more by setting stability and the percentage of the total resistance in use (at the wiper) than by fundamental resistance change due to temperature alone. The parameter shown in table 2 is a 2 s distribution typifying the behavior of the device when used with 40 % or more of the total resistance in use.
- (3) Derated linearly for full power at + 85 °C to zero power at + 150 °C. See figure 2.
- (4) All ΔR 's are measured to the tolerance specified + 0.01 Ω .
- (5) Whichever is greater.
Special available options:
Special marking
Power conditioning and screening operations.

VFR TRIMMERS ARE INSPECTED

100 % for:


- Immersion
- Resistance tolerance check
- End resistance
- Visual-mechanical
- Dynamic tests for continuity, CRV

By sample for:

- TCR
- DWV

TABLE 6 - GLOBAL PART NUMBER INFORMATION

NEW GLOBAL PART NUMBER: Y0069500R000J0L (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y0069 500R000 J 0 L:

TYPE: 1260W


VALUE: 500.0 Ω

ABSOLUTE TOLERANCE: $\pm 5.0\%$

TERMINATION: tin/lead

PACKAGING: foam/box pack

HISTORICAL PART NUMBER: 1260W 500R00 J B B (will continue to be used)



Note

⁽¹⁾ For non-standard requests, please contact application engineering.

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.