




3-6450830-2 Product Details




3-6450830-2

TE Internal Number: 3-6450830-2



Active



View 3D PDF

MULTI-BEAM XL and MULTI-BEAM XLE Connectors



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Product Series = XLE
- Board-to-Board
- Header
- Connector Style = Plug
- Contact Type = Pin

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [RIGHT ANGLE WITH SHORT GUIDES AND LP CONTACTS ASSEMB...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [2 PIECE POWER CONNECTORS grq 4-1773458-1](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version J2)
- [3D Model](#) (IGES, Version J2)
- [3D Model](#) (STEP, Version J2)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Series](#) = XLE
- Connector Type = Header
- [Mount Angle](#) = Right Angle
- [Termination Style](#) = Solder
- [Mating Type](#) = Blindmate
- [PCB Mount Retention](#) = With
- Guides = With

Electrical Characteristics:

- Mating Functionality = Mate First-Break Last, Select Load
- Voltage Rating (Signal) (VAC) = 60
- Voltage Rating (Power) (VDC) = 200

Termination Features:

- Termination Post Length (mm [in]) = 3.43 [0.135]

Body Features:

- [Sequencing](#) = Yes
- [PCB Mount Retention Type](#) = Boardlock(s)
- Connector Configuration Orientation = Left-to-Right
- Centerline, DC Module (mm [in]) = 6.35 [0.250]
- Centerline, AC Module (mm [in]) = 7.62 [0.300]
- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

Contact Features:

- Contact Type = Pin
- Contact Material (Power) = High Conductivity Copper
- Contact Material (Signal) = High Conductivity Copper
- Contact Plating, Mating Area, Material = Gold (30)

Housing Features:

- Connector Style = Plug
- Housing Material = High Temperature Thermoplastic

Configuration Features:

- [Total Number of DC Power](#) = 3
- [Total Number of AC Power](#) = 4
- Total Number of Coax = 0
- [Total Number of Signal](#) = 12
- Connector Contact Configuration (No. of Pos./Type) = 4/AC Power, Blank, 12/Signal, 3/DC Power

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application Use = Board-to-Board

Other:

- Brand = AMP
- Comment = For additional configurations available, contact Tyco Electronics.; Variable PCB dimensions, see customer drawing.; No contacts loaded in positions P 1 and P 3.

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

