




[+ HARNESSING](#)
[HEAT SHRINK BOOTS](#)



✓ Active

TE CONNECTIVITY (TE)
202A121-25-0
[Raychem](#) | [CAP](#) , [CRPS](#)

202A121-25-0
TE Internal Number: 806696-000
Alias ID: 5-1196241-2

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Lipped No

Operating Temperature Range (°C) -75 – 150

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options S1048 Separate Adhesive, -55°C – 105°C (-67°F – 221°F), S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)

Material Systems Code 25

 **PRODUCT DRAWING**
[English](#)

DOCUMENTATION

Product Drawings

Boot, Straight, Overexpanded
PDF
English

Product Specifications

Product Specification

Thermofit Elastomeric Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable
PDF
English

-25 MOULDED PARTS
PDF
English

Product Environmental Compliance

Safety Data Sheet

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped No

Body Features

Material Systems Code 25
Adhesive Pre-Coat No
Material Modified Elastomer

Dimensions

Cable Diameter Range 5.3 – 17.8 mm [.209 – .701 in]
Wire/Cable Outside Diameter .236 in, .276 in, .3 in, .31 in, .35 in, .39 in, .43 in, .433 in, 10 mm, 11 mm, 6 mm, 7 mm, 8 mm, 9 mm

Usage Conditions

Operating Temperature Range (°C) -75 – 150

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No
Approved Standards BS-G-198-5-DE, DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867

Other

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures
Adhesive Options S1048 Separate Adhesive, -55°C – 105°C (-67°F – 221°F), S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F)
Adhesive Type Adhesive Purchased Separately

Statement of Compliance

Statement of Compliance
PDF