Data sheet

# QL 10 SAKS4

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

| | |
|---|---|
| Version | Cross-connector (terminal), when screwed in, grey, 47 A, Number of poles: 10, Pitch in mm (P): 10.00, Insulated: No, Width: 226 mm |
| Order No. | 0339000000 |
| Type | QL 10 SAKS4 |
| GTIN (EAN) | 4008190025335 |
| Qty. | 20 items |



Downloaded from Arrow.com.

# Data sheet

## QL 10 SAKS4

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 4 mm | Depth (inches) | 0.1575 inch |
| Height | 10 mm | Height (inches) | 0.3937 inch |
| Width | 226 mm | Width (inches) | 8.8976 inch |
| Net weight | 69.74 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Material data

| | | | |
|---|---|---|---|
| Basic material | Copper | Colour | grey |

### System specifications

| | |
|---|---|
| Version | for cross-connection link |

### Additional technical data

| | | | |
|---|---|---|---|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | | |

### Dimensions

| | |
|---|---|
| Pitch in mm (P) | 10.00 mm |

### General

| | | | |
|---|---|---|---|
| Number of poles | 10 | Installation advice | Direct mounting |

### Rating data

| | | | |
|---|---|---|---|
| Rated voltage | 400 V | Nominal current | 47 A |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |



Downloaded from Arrow.com.