


Color: white



Dimensions in mm

Strain relief housing *WINSTA*® MIDI 3-pole

When using the strain relief housing from the *WINSTA*® MIDI product line, error-free installation is ensured. An extensive range of accessories rounds out the *WINSTA*® product line from WAGO. *WINSTA*® MIDI with Push-in CAGE CLAMP® spring pressure connection technology is used in can be found in a variety of projects you can use for quick, easy, flexible, and secure installation. A range up to 55 mm can be used for the strip length.

Lower costs through fast commissioning and elimination of service expenses – solutions from *WINSTA*® MIDI

The *WINSTA*® Pluggable Connection System is perfectly tailored to the very strict requirements of building installation. It makes electrical installation pluggable, and therefore more efficient, even more reliable, and error-free. Using this pre-assembled system reduces assembly times and installation errors at the construction site. Enjoy the benefits of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismatching from WAGO.

- for automation controllers
- quick replacement of defective units during ongoing operation

Connection data	
Connection 1	
Pole number	3
Connectable sheathed cable diameter	8 ... 11.5 mm
Strip length (outer insulation)	55 mm



Physical data		
Pin spacing	10 mm / 0.394 inches	

Material data		
Note (material data)	Information on material specifications can be found here	
Color	white	
Insulation material (main housing)	Polyamide (PA66)	
Flammability class per UL94	V0	
Fire load	0.32 MJ	
Weight	11 g	

Environmental requirements		
Processing temperature	-5 ... +40 °C	
Continuous operating temperature	-35 ... +85 °C	
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C	

Commercial data		
Product Group	20 (Winsta)	
PU (SPU)	25 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4044918102438	
Customs tariff number	85369010000	

Product classification		
UNSPSC	39121402	
eCl@ss 10.0	27-44-06-92	
eCl@ss 9.0	27-44-06-92	
ETIM 9.0	EC002863	
ETIM 8.0	EC002863	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant, No Exemption	

Approvals / Certificates		
General approvals		
		
Approval	Standard	Certificate Name
cURus Underwriters Laboratories Inc.	UL 1977	E45171

Approvals for marine applications		
 		
Approval	Standard	Certificate Name
DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAE00001Z6
LR Lloyds Register	IEC 61984	LR22429487TA



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
770-513/032-000

↓

Documentation

Bid Text			
770-513/032-000	19.02.2019	xml 2.78 KB	↓
770-513/032-000	04.12.2014	doc 23.50 KB	↓

CAD/CAE-Data

CAD data		CAE data	
2D/3D Models 770-513/032-000	↓	WSCAD Universe 770-513/032-000	↓
		ZUKEN Portal 770-513/032-000	↓

- 1 Compatible Products
- 1.1 Optional Accessories
- 1.1.1 Marking
- 1.1.1.1 Marking strip



Item No.: 210-333
Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive; white