

1XE97

M

DRAWING
NUMBER

2

ISSUE

REPLACES

PR-20069

CHECK

CHECK

CHECK

T S M

11 MAY 92


DRAWN

REVISIONS

A PR20069

TSM
11 MAY 92

DM/CAD




NOTES

- (1) MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 $\pm .002$ CENTERS
- (2) ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- (3) WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .55 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — — 5-17 OZ
RELEASE FORCE — — — — 4 OZ MIN
RELEASE TRAVEL — — — — .004 MIN
DIFFERENTIAL TRAVEL — — .005 MAX
OVERTRAVEL — — — — .004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

28 VOLTS DC RATING

INDUCTIVE — — — SEA LEVEL — — — 4 AMP
50,000 FT — — — 2.5 AMP
RESISTIVE — — — SEA LEVEL — — — 7 AMP
50,000 FT — — — 7 AMP

115 VOLTS 400 CYCLES — — — SEA LEVEL

RESISTIVE — — — — — 7 AMP
INDUCTIVE — — — — — 4 AMP
LAMP — — — — — 1 AMP
MOTOR — — — — — 1.5 AMP

SCALE 2:1

DO NOT
SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT (3)