




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	APR23/20	L.CHAN



RECOMMENDED PANEL CUTOUT

MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
(FLAT) PLATING: 30 μ" [0.76 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ" [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH TIN FINISHED ON SOLDER TAILS.


RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM
FOR 5 SEC MAXIMUM.

AMPHENOL PART NUMBER: RJHSE-KP80

RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

LOCATE HOLES
⌀ ⌀.005[0.13]

POSITION DIMENSIONS
ARE BASIC

UNLESS SPECIFIED OTHERWISE		DRAWN <i>W.QIU</i>		DATE <i>APR23/20</i>		Amphenol Canada Corp. Commercial Products					
PRIMARY UNITS INCHES		CHECKED <i>L.CHAN</i>		DATE <i>APR23/20</i>							
SECONDARY MILLIMETERS		M.E. APP'D				TITLE SINGLE PORT MODULAR JACK, VERTICAL MOUNT, 8 POSITIONS, 8 CONTACTS, WITHOUT LED, WITHOUT FLANGE—RoHS COMPLIANT					
REFERENCE IN PARENTHESES		Q.A. APP'D									
GENERAL TOLERANCES		DWG APPR.									
1 DECIMAL PLACE ±.025		ENG. REL. NO.				DWG. NO. <i>P-RJHSE-KP80</i>				REV <i>A</i>	
2 DECIMAL PLACES ±.020		REF.									
3 DECIMAL PLACES ±.015		THIRD ANGLE PROJECTION				DO NOT SCALE DRAWING		CODE ID NO. 03554 DWG SIZE: C SCALE: <i>3/1</i> SHEET <i>1</i> OF <i>1</i>			
ANGULAR DEGREES ±1.0°											

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.