Part Number : 1200110330
Product Description : M12 Signal, A-Coded, Receptacle, 8 Poles, Female, Front Panel Mount, M14x1.0 Mounting Threads, 0.34mm² (22 AWG), PVC Leads, 0.30m (0.984') Length
Series Number : 120011
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 8R8E30E03C3003

Documents and Resources

Drawings

1200110330_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/108/2014 (17 Dec 2014)
EU RoHS	Not Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120011
Description	M12 Signal, A-Coded, Receptacle, 8 Poles, Female, Front Panel Mount, M14x1.0 Mounting Threads, 0.34mm² (22 AWG), PVC Leads, 0.30m (0.984') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	883906176105

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	A-Coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M14 x 1.0
Orientation	Straight

Downloaded from Arrow.com.

Panel Mount	Front
Poles	8
Temperature Range - Operating	-25° to +105°C
Wire/Cable Type	PVC Leads, UL 1061
Wire Size (AWG)	22

Downloaded from Arrow.com.