




TE Connectivity. All Rights Reserved.									
REVISIONS									
P	LTR	DESCRIPTION					DATE	DWN	APVD
A1		REVISED	PER	ECN-21-122181			26OCT2021	RZ	WK


1. USE INSTRUCTION SHEET 408-2299-5.



RECOMMENDED STRIP LENGTH
NO SCALE
FOR 5225554-2 AND 5225554-6



RECOMMENDED STRIP LENGTH
NO SCALE
FOR 5225554-9 AND 1-5225554-1



RG-393/U	220015-1	332022	9-225490-1	225471-7	9-225518-0	B	1-5225554-1
RG-9/U, 9A/U & 214/U	220015-1	332022	9-331987-3	225599-1	9-225518-0	B	5225554-9
RG-142/U, 142A/U, 142B/U	220045-2	-	9-225560-4	225471-3	9-225518-2	A	5225554-6
RG-58A/U, 58C/U	220045-2	-	9-225560-5	225471-1	9-225518-1	A	5225554-2
CABLE	CRIMP TOOL	④ SEAL QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSEMBLY QTY=1	VIEW	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DICKS CHK J. HAVENER APVD J. LIPPERT	18APR2005 18APR2005 18APR2005	TE Connectivity	
DIMENSIONS: mm (INCHES)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0. PLC ± - 1. PLC ± - 2. PLC ± 0.41 [016] 3. PLC ± - 4. PLC ± - ANGLES ± -		PRODUCT SPEC 108-12001		PLUG, RIGHT ANGLE, WEATHERPROOF, TNC	
MATERIAL -		FINISH -		APPLICATION SPEC 408-2299-5	
WEIGHT 0.000000		A100779		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1	