

FO-55111-A

HONEYWELL
PART NUMBER
311SM2-H58

PRODUCT CODE
TZA1138

REV	DOCUMENT	CHANGED BY	CHECK
8	0038113	PRS 12JUN08	BLR

B


A

A

B

A

A



NOTE -

1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS

2 PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES.

3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO. SR - 12940

REPLACES -

CHARACTERISTICS

OPERATING FORCE - - 30 GRAM MAX

RELEASE FORCE - - - - 5 GRAM MIN

DIFFERENTIAL TRAVEL - - .027 MAX

OVERTRAVEL - - - - .026 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT S P D T			
30 VOLTS DC RATING			
	SEA LEVEL	50,000 FT	
INDUCTIVE	3 AMP	2.5 AMP	
RESISTIVE	5 AMP	5 AMP	
MAXIMUM INRUSH 24 AMP			
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	 05 
	UL, CSA	5A, <u>250</u> VAC ~  	BRAND L4

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE X ±

ONE PLACE .X ±

TWO PLACE .XX ±

THREE PLACE .XXX ±

FOUR PLACE .XXXX ±

ANGLES ±

THIRD ANGLE PROJECTION

DRAWN	VK	31 OCT 07
CHECK	RJ	31 OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	311SM2-H58	8
SCALE	-	WEIGHT .006 LB	SHEET 1 OF 1