



Part Number : [1300488006](#)

Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Pigtail, 26 AWG, PVC Cable, 20.0m (65.62') Length

Series Number : 130048

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : E10A00615M200

Documents and Resources

Drawings

[1300488006 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130048
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Pigtail, 26 AWG, PVC Cable, 20.0m (65.62') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906557270

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Cable Diameter	5.59mm (.220")
Cable Length	20.0m (65.62')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass

Material - Plating Mating	Gold
Net Weight	938.395/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	N/A
Wire Size (AWG)	26

This document was generated on Dec 29, 2025