





	1	2	3	4	5	6	7																																																																																																		
A	 ② Dimension ③ <table><tr><td>DIM A</td><td>(N-1)x3.81+5.0</td></tr><tr><td>DIM B</td><td>(N-1)x3.81</td></tr></table> N=Number of poles <table><tr><th>Poles</th><th>Tolerance</th></tr><tr><td>2P-6P</td><td>±0.15</td></tr><tr><td>7P-12P</td><td>±0.20</td></tr><tr><td>13P-18P</td><td>±0.25</td></tr><tr><td>19P-24P</td><td>±0.30</td></tr></table> ② Material Item ① Male contact pin: Copper Tin plated Item ② Terminal(housing):Thermoplastic (UL94V-0) Green(RAL6018/T) Electrical cULus/VDE Voltage rating: 300V/300V Current rating: 10A/10.5A Withstanding Voltage: 1.6KV/2.5KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  							DIM A	(N-1)x3.81+5.0	DIM B	(N-1)x3.81	Poles	Tolerance	2P-6P	±0.15	7P-12P	±0.20	13P-18P	±0.25	19P-24P	±0.30	A																																																																																			
DIM A	(N-1)x3.81+5.0																																																																																																								
DIM B	(N-1)x3.81																																																																																																								
Poles	Tolerance																																																																																																								
2P-6P	±0.15																																																																																																								
7P-12P	±0.20																																																																																																								
13P-18P	±0.25																																																																																																								
19P-24P	±0.30																																																																																																								
B								B																																																																																																	
C								C																																																																																																	
D	 							D																																																																																																	
E	 Recommended P.C.B LAYOUT							E																																																																																																	
F								F																																																																																																	
G	RoHS compliant Unit: mm <table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>10.12.2009</td><td>Dean</td><td></td></tr><tr><td>X.</td><td>±0.50</td><td>④</td><td>Update the dimension</td><td>09.01.2015</td><td>Amy</td><td>Approved</td><td>09.01.2015</td><td>Amy</td><td>ASSMANN WSW-No.</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>A-TB381-OQxxCV</td></tr><tr><td>X.XX</td><td>±0.10</td><td>③</td><td>Update</td><td>13.03.2013</td><td>Amy</td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>②</td><td>Update</td><td>06.03.2013</td><td>Amy</td><td colspan="3" rowspan="2"></td><td>Drawing-No.</td></tr><tr><td>X.°</td><td>±1°</td><td>①</td><td>Drawn</td><td>10.12.2009</td><td>Dean</td><td>ASS 3829 CO</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>rev04</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>Sheet</td></tr><tr><td></td><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td></tr></table>							Scale	Free						Date	Name	Customer-No.	TOLERANCE						Drawn	10.12.2009	Dean		X.	±0.50	④	Update the dimension	09.01.2015	Amy	Approved	09.01.2015	Amy	ASSMANN WSW-No.	X.X	±0.30								A-TB381-OQxxCV	X.XX	±0.10	③	Update	13.03.2013	Amy					DIM	TOL	②	Update	06.03.2013	Amy				Drawing-No.	X.°	±1°	①	Drawn	10.12.2009	Dean	ASS 3829 CO										rev04										Sheet		Angle	TOL	Id.	Modification	Date	Name				G
Scale	Free						Date	Name	Customer-No.																																																																																																
TOLERANCE						Drawn	10.12.2009	Dean																																																																																																	
X.	±0.50	④	Update the dimension	09.01.2015	Amy	Approved	09.01.2015	Amy	ASSMANN WSW-No.																																																																																																
X.X	±0.30								A-TB381-OQxxCV																																																																																																
X.XX	±0.10	③	Update	13.03.2013	Amy																																																																																																				
DIM	TOL	②	Update	06.03.2013	Amy				Drawing-No.																																																																																																
X.°	±1°	①	Drawn	10.12.2009	Dean				ASS 3829 CO																																																																																																
									rev04																																																																																																
									Sheet																																																																																																
	Angle	TOL	Id.	Modification	Date	Name																																																																																																			
H								H																																																																																																	
	1	2	3	4	5	6	7	SV3142																																																																																																	